


# Molded Case Circuit Breakers

## External Accessories

### Door-Mounted Operators

## Section 3



TDM Operating Handle, Fixed or Adjustable Shaft

### TDM Handle Operating Mechanisms, Door Mounted

Complete mechanism with handle UL listed, E-57253

Operating mechanism only, UL Component Recognized, E-57253

Breaker Type	Box Depth in Inches	Complete Mechanism <sup>1</sup> with NEMA 1, 3R, 12 Handle		Operating Mechanism Only		Handle Only			
		Product Number	List Price GO-144	Product Number	List Price GO-144	NEMA 1, 3R, 12		NEMA 4/4X	
						Product Number	List Price GO-144	Product Number	List Price GO-144
TQD, THQD	Shallow Mount 3 7/16	TQDHM1	\$69.00	TQDOM1	\$42.00				
	Extended Shaft 4 5/16 - 14 5/16	TQDHM2	\$82.00	TQDOM2 <sup>2</sup>	\$55.00				
TEB, TEC, TB1, TED, THED	Shallow Mount 4 3/16	TEFHM1	\$69.00	TEFOM1	\$42.00				
	Extended Shaft 5 1/8 - 5 7/32 5 1/8 - 5 13/16 5 1/8 - 15	TEFHM3	\$82.00	TEFOM3	\$55.00	TH1	\$27.00		
		TEFHM4	\$82.00	TEFOM4	\$55.00				
		TEFHM2	\$82.00	TEFOM2	\$55.00				
TFC, TFJ, TFK, THFK	Shallow Mount 5 7/8	TFKHM1	\$103.50	TFKOM1	\$76.50			THCH45 <sup>3,4</sup>	\$303.00
	Extended Shaft 6 7/8 - 15 1/2	TFKHM2	\$107.50	TFKOM2 <sup>2</sup>	\$80.50				
TJC, TJD, TJJ, TJK, THJK, TB4, TBC4	Shallow Mount 5 7/8	TJKHM1	\$143.00	TJKOM1	\$102.00				
	Extended Shaft 5 5/8 - 15 5/8	TJKHM2	\$147.00	TJKOM2 <sup>4</sup>	\$106.00	TH2	\$41.00		
TKC, TKM, THKM, TB6, TBC6, TB8, TBC8	Shallow Mount 7 7/16	TKMHM1	\$143.00	TKMOM1	\$102.00				
	Extended Shaft 7 1/32 - 17 5/16	TKMHM2	\$147.00	TKMOM2 <sup>4</sup>	\$106.00				
SE150 (GEH-5611) <sup>5</sup>	4 3/16	SEFHM1	\$79.00	SEFOM1	\$52.00	TH1	\$7.00		
	6 1/8 - 15	SEFHM2	\$81.50	SEFOM2 <sup>2</sup>	\$55.00				
SF250 (GEH-5611) <sup>5</sup>	5 7/8	SEFHM1	\$79.00	SEFOM1	\$52.00			THCH45 <sup>3,4</sup>	\$303.00
	7 3/4 - 15 1/2	SEFHM2	\$81.50	SEFOM2 <sup>2</sup>	\$55.00				
SG600 (GEH-5653) <sup>5</sup>	5 7/8	SGHM1	\$143.00	SGOM1	\$102.00	TH2	\$41.00		
	5 5/8 - 15 5/8	SGHM2	\$147.00	SGOM2 <sup>4</sup>	\$106.00				
SK1200 (GEH-5612) <sup>5</sup>	6	SKHM1	\$143.00	SKOM1	\$102.00				
	7	SKHM2	\$147.00	SKOM2 <sup>4</sup>	\$106.00				

<sup>1</sup>Handle assembly and operating mechanism separately packaged.

<sup>2</sup>For 15-inch long shaft order Product Number 788A831G10, List Price \$40.00, GO-135B. For 20-inch long shaft order Product Number 788A831G21 List Price \$40.00, GO-135B.

<sup>3</sup>Provides interlocking for J600, SG600 SK1200, and K1200 breakers when used with the extended shaft operating mechanism. For interlocking with E150/SE150, F225 and SF250 order special shaft Product Number 788A832G1, List Price \$40.00, GO-135B.

<sup>4</sup>For 15-inch long shaft order Product Number 788A832G2, List Price \$40.00, GO-135B. For 20-inch long shaft order Product Number 788A832G5, List Price \$40.00, GO-135B.

<sup>5</sup>Installation instructions publication number.

<sup>6</sup>MOD 1 is 7 7/16; MOD 2 is 8 3/32.

<sup>7</sup>MOD 1 is 7 3/16 - 17 3/16; MOD 2 is 7 15/16 - 17 15/16.

### Handle Accessories for TDM Operating Mechanisms

Device	Product Number	List Price GO-139
Replacement neoprene gaskets for NEMA 1, 3R and 12 enclosures		
Use with TH1	788A742P3	\$2.80
Use with TH2	788A742P4	\$6.10

