

2-120-T Aurora GU10



With a myriad of reflector, trim, and color temperature combinations, Aurora blends discretely with any décor. The 2 1/2" regressed lamp delivers high lumens without glare, while 35° aiming increases flexibility in locating luminaires.

FEATURES

- Utilizes GU10
- 35° aiming
- Die-cast aluminum fixture
- Powder coated and plated trim ring finishes
- Trim clips designed for 5/8" ceiling thickness
- Accepts up to 2 optional media
- Clear glass lens included
- Trimless version available (see separate specifications)

DETAILS


Trim Class: 4"
Category: Recessed Downlight
Shape: Round
Adjustability: Tilt




2-120-T-Aurora-GU10-Specs • Subject to change without notice • Rev 2018.11.16 • 1/4

Features & Lighting

DIMENSIONS



CEILING CUTOUT



FLANGE FINISHES

- White
- Chrome Plated
- Black
- Matte Silver
- Bronze
- Gold Plated
- Matte Nickel

REFLECTOR FINISHES

- Black Open
- Black Specular
- Black Stepped Baffle
- Champagne Specular
- Copper Specular
- Gold Specular
- Mocha Brushed
- Silver Specular
- White Open
- White Stepped Baffle
- Champagne Satin
- Copper Satin
- Gold Satin
- Nickel Satin
- Silver Satin

2-120-T-Aurora-GU10-Specs • Subject to change without notice • Rev 2018.11.16 • 2/4

2-120-T Aurora GU10

Project

Type

Notes

Product Code

1 2 3 4 5 6

1. Trim

2-120-T Aurora

2. Lamp

GU10 Halogen

3. Flange Finish

01 White
02 Chrome Plated
04 Black
05 Matte Silver
06 Bronze
09 Gold Plated
11 Matte Nickel
CC Custom Color¹

4. Reflector Finish

BLO Black Open
BA Black Specular
BLS Black Stepped Baffle
CHA Champagne Specular
CHAS Champagne Satin
COPA Copper Specular
COPAS Copper Satin
GA Gold Specular
GAS Gold Satin
MOCH Mocha Brushed
NICS Nickel Satin
SA Silver Specular
SAS Silver Satin
WHO White Open
WHS White Stepped Baffle

5. Optional Media (2 Maximum)

CL Clear
EL Elongating
FRO Frosted
HC Honeycomb
PER Perimeter Frosted
SL Solite Softening
SPDL Spread

6. Options

EXT Extension Clips (Maximum 2")

Notes

¹ CC custom color requires consultation with Lightheaded sales personnel.

2-120-T-Aurora-GU10-Specs • Subject to change without notice • Rev 2018.11.16 • 4/4