



### ▶▶ Modular Crimper

Fluke Networks all-in-one crimping tool for WESS type 6- and 8-position modular telephone plugs. Crimps 8-position RJ-45 connectors and 4- and 6-position RJ-11 and RJ-12 connectors.

- Embedded flat cable cutter and stripper

Model	Description
11212530	Modular crimper



### ▶▶ Cable Splicing Knife

Fluke Networks cable splicing knife is the perfect tool for splitting cable sheaths. Soft, easy-to-grip handle and cutlery-steel blade for durability and long-lasting blade edge.

- Short blade (1.75 in) for strength
- Cutlery-steel blade for durability
- No slip, easy-to-grip handle
- Cuts various insulation types

Model	Description
44400000	Cable splicing knife



### ▶▶ D-Snips™

Fluke Networks Electrician's D-Snips™ offer a unique ergonomically-designed handle that leverages your power, providing 1½ times the cutting force with half the effort.

- Ergonomic design provides 1½ times the cutting force with half the effort
- High-quality forged steel construction for strength and durability
- File and scraper on both blades for cleaning wire
- Notched blade for stripping 19- and 23-gauge wire
- Cuts up to 16-gauge solid and 12-gauge stranded wire

Model	Description
44300000	D-Snips



### ▶▶ Electrician's Snips

These versatile electrician's snips feature a file and scraper on both blades for easy wire cleaning. They also feature a handy notched scissor blade for quickly stripping 19- and 23-gauge wire. Made to last with high-quality forged steel, these snips are a must have for your tool bag.

- High-quality forged steel construction for strength and durability
- File and scraper on both blades for cleaning wire
- Notched blade for stripping 19- and 23-gauge wire
- Cuts up to 16-gauge solid and 12-gauge stranded wire
- Serrated blade for non-slip wire cutting

Model	Description
44500000	Electrician's snips



### ▶▶ Cable Strippers

Fluke Networks line of cable strippers includes a double slotted cable stripper for 22/24 AWG wire installation and a coax stripper to perform 2-level and 3-level stripping of RG58/59 coaxial cables. We also offer a combo stripper that cuts and rings Teflon®, smoothly slits fiber, copper and coaxial cables, and rings 25-100 pair cable.

- Full line of cable strippers offered
- Round cable stripper for a variety of flexible round cable
- Coax strippers with two or three levels



### ▶▶ Need-L-Lock™ Crimping Pliers

The Need-L-Lock pliers' patented four-in-one tool combines UR/UY/UG connector crimper with needle-nose pliers so you can carry one less tool on your belt. Aligned crimping jaws come down square ensuring a solid connection. Jaws are grooved to provide a better grip on wires and feature a built-in cutter and wire stripper.

- Needle nose pliers
- UR/UY/UG connector crimper
- Wire stripper hole
- Built-in side cutter
- Rubber coated handles for non-slip grip

### ▶▶ Probe Pic

Fluke Networks handy, pocket-sized insulation probe is ideal for checking for loose or damaged connections or to spread apart wires for direct access. Its compact size also makes it perfect for using the pic end for tracing or pulling wires from a bunch.

- Trace and pull wires with the pic end
- Check for loose or damaged connections
- Spread apart wires for direct access
- Compact size



### ▶▶ Can Wrench

Fluke Networks can wrenches allow universal access to telephone boxes and pedestals. Open telephone box fasteners and tightens nuts on binding post terminals.

- Two hex head sockets (7/16 inch and 3/8 inch)
- Color-coded socket ends for quick size identification
- Wrench body constructed of tough, impact resistant and abrasion resistant material
- Socket ends guaranteed not to split or break up to a maximum torque of 45 pounds
- Two models available with wire stripper in handle (22 or 24 gauge)



Model	Description
11230002	Cable stripper (round cable)
44210013	Double slotted stripper with cutter, 22/24 gauge
44200013	Double slotted stripper 22/24 gauge
11231257	Coax stripper, 2-level
11231255	Coax stripper, 2 and 3-level

Model	Description
11294000	Need-L-Lock crimping pliers

Model	Description
44600000	Probe pic, 105 degree

Model	Description
44007000	Can wrench, hex head
44507003	Can wrench with stripper, 22 gauge
44507004	Can wrench with stripper, 24 gauge
10660001	Security key insert