



## 2-120-T Aurora MR16



With a myriad of reflector, trim, and color temperature combinations, Aurora blends discretely with any décor. The 2 1/2" regressed lamp delivers high lumens without glare, while 35° aiming increases flexibility in locating luminaires.

### FEATURES

- Utilizes MR16
- 35° aiming
- Die-cast aluminum fixture
- Powder coated and plated trim ring finishes
- Trim clips designed for 5/8" ceiling thickness
- Accepts up to 2 optional media
- Clear glass lens included
- Trimless version available (see separate specifications)

### DETAILS

Trim Class: 4"  
Category: Recessed Downlight  
Shape: Round  
Adjustability: Tilt




---


2-120-T-Aurora-MR16-Specs • Subject to change without notice • Rev 2018.11.16 • 1/4

# Features & Lighting

## DIMENSIONS



## CEILING CUTOUT



## FLANGE FINISHES

- White
- Chrome Plated
- Black
- Matte Silver
- Bronze
- Gold Plated
- Matte Nickel

## REFLECTOR FINISHES

- Black Open
- Black Specular
- Black Stepped Baffle
- Champagne Specular
- Copper Specular
- Gold Specular
- Mocha Brushed
- Silver Specular
- White Open
- White Stepped Baffle
- Champagne Satin
- Copper Satin
- Gold Satin
- Nickel Satin
- Silver Satin

2-120-T-Aurora-MR16-Specs • Subject to change without notice • Rev 2018.11.16 • 2/4

# 2-120-T Aurora MR16

Project

Type

Notes

Product Code

1 2 3 4 5 6

1. Trim

**2-120-T** Aurora

2. Lamp

**MR16** Halogen

3. Flange Finish

**01** White  
**02** Chrome Plated  
**04** Black  
**05** Matte Silver  
**06** Bronze  
**09** Gold Plated  
**11** Matte Nickel  
**CC** Custom Color<sup>1</sup>

4. Reflector Finish

**BLO** Black Open  
**BA** Black Specular  
**BLS** Black Stepped Baffle  
**CHA** Champagne Specular  
**CHAS** Champagne Satin  
**COPA** Copper Specular  
**COPAS** Copper Satin  
**GA** Gold Specular  
**GAS** Gold Satin  
**MOCH** Mocha Brushed  
**NICS** Nickel Satin  
**SA** Silver Specular  
**SAS** Silver Satin  
**WHO** White Open  
**WHS** White Stepped Baffle

5. Optional Media (2 Maximum)

**CL** Clear  
**EL** Elongating  
**FRO** Frosted  
**HC** Honeycomb  
**PER** Perimeter Frosted  
**SL** Solite Softening  
**SPDL** Spread

6. Options

**EXT** Extension Clips (Maximum 2")

Notes

<sup>1</sup> CC custom color requires consultation with Lightheaded sales personnel.

2-120-T-Aurora-MR16-Specs • Subject to change without notice • Rev 2018.11.16 • 4/4