

## TBQC Interposing Terminal Block

| Part Number | Description  | Lifecycle Status |
|-------------|--|------------------|
| IC693ACC329 | Interposing terminal block base for IC694MDL645, IC694MDL646, and IC694MDL240. The base can also be used with any 20 point terminal discrete or analog modules not listed. | Active           |
| IC693ACC330 | Interposing terminal block base for IC694MDL740 and IC694MDL742  | Discontinued     |
| IC693ACC331 | Interposing terminal block base for IC694MDL741  | Discontinued     |
| IC693ACC332 | Interposing terminal block base for IC694MDL940  | Active           |
| IC693ACC333 | Interposing terminal block base for IC694MDL340  | Active           |
| IC693ACC337 | Interposing terminal block base for IC693MDL654/655/752/753 and IC694MDL654/655/752/753  | Active           |

## TBQC Cables

| Part Number | Description   | Lifecycle Status |
|-------------|---|------------------|
| IC693CBL327 | Cable, Left Side, One -24 Pin 90 Degree Connector, 3 Meter. Cable has a connector on only one end and open on the other. Cable used with TBQC I/O Face Plate Adapter or Fujitsu style I/O modules.  | Active           |
| IC693CBL328 | Cable, Right Side, One -24 Pin 90 Degree Connector, 3 Meter. Cable has a connector on only one end and open on the other. Cable used with TBQC I/O Face Plate Adapter or Fujitsu style I/O modules. | Active           |
| IC693CBL329 | Cable, Left Side, One -24 Pin 90 Degree Connector, 1 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.  | Active           |
| IC693CBL330 | Cable, Right Side, One -24 Pin 90 Degree Connector, 1 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.   | Active           |
| IC693CBL331 | Cable, Left Side, One -24 Pin 90 Degree Connector, 2 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.  | Active           |
| IC693CBL332 | Cable, Right Side, One -24 Pin 90 Degree Connector, 2 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.   | Active           |
| IC693CBL333 | Cable, Left Side, One -24 Pin 90 Degree Connector, 0.5 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.  | Active           |
| IC693CBL334 | Cable, Right Side, One -24 Pin 90 Degree Connector, 0.5 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.   | Active           |

## High Density Terminal Block Quick Connect (32 point I/O terminals)

High Density Terminal Block Quick Connect (TBQC) for selected I/O modules enables the user to easily connect interposing terminal blocks. The HDTBQC consist of a I/O module terminal block with a 40 pin Fujitsu male connector, cable and interposing terminal block. The HDTBQC is compatible with modules that accept IC694TBC032 (24 VDC discrete inputs and analog input and output modules. The HDTBQC is not compatible with discrete output modules).

## HDTBQC I/O Module Face Plate Adapter

| Part Number | Description   | Lifecycle Status |
|-------------|---|------------------|
| IC694TBC032 | High-density, 36-point, terminal block with cable connector.<br>IC695ALGxxx, IC69xMDL660 and IC694MDL664 modules only. Discrete output modules not supported. | Active           |

## HDTBQC Interposing Terminal Block

| Part Number | Description  | Lifecycle Status |
|-------------|--|------------------|
| IC694RTB032 | High-density remote base, 36-point, with shield ground lug and removable terminal blocks.<br>IC695ALGxxx, IC69xMDL660 and IC694MDL664 modules only. Discrete output modules not supported. | Active           |

## HDTBQC Interface Cables

| Part Number | Description   | Lifecycle Status |
|-------------|---|------------------|
| IC694CBL005 | Shielded 0.5 meter cable with termination on both ends. IC694TBC032 and IC694RTB032 only.   | Active           |
| IC694CBL010 | Shielded 1.0 meter cable with termination on both ends. IC694TBC032 and IC694RTB032 only.   | Active           |
| IC694CBL030 | Shielded 3.0 meter cable with termination on both ends. IC694TBC032 and IC694RTB032 only.   | Active           |
| IC694CBL130 | Shielded 3.0 meter cable with termination on one end that connects to the IC694TBC032 terminal block. The other end of the cable is non-terminated wires. | Active           |