



**RACO**

**TAYMAC**

**BELL**

COMMERCIAL, INDUSTRIAL AND RESIDENTIAL ELECTRICAL PRODUCTS




**TAYMAC**


# U • CONDUIT 10-IN-1

## UNIVERSAL CONDUIT BODY FOR RIGID/IMC OR EMT

*Easily configures to all standard bodies (LB • LR • LL • T • C)*



### FEATURES

- Patented interchangeable panels can be configured to LB, LR, LL, T or C
- Suitable for weatherproof installs
- Use set screws for EMT conduit, and threaded hubs for threaded Rigid/IMC conduit or fittings
- Available in trade sizes 1/2", 3/4" and 1"
- Lightweight, Durable TAYMAC TUFF Die Cast Aluminum Construction
- Seamless pre-affixed gasket and self-aligning covers/panels
- More wiring capacity than standard bodies and meets 2014 NEC 314.16(C)(2) for volume marking
- Tri-combo head set screws 
- Unique design lends to easy and time-saving installations
- Captive screws with attached O-ring for ease of use and a weatherproof seal
- Includes 4 steel reducer bushings in the 1" size – (2) 1" to 3/4", (2) 1" to 1/2"; and (2) 3/4" to 1/2" bushings in the 3/4" size\*
- Not suitable for use in hazardous location applications
- Includes (1) body, (3) blank covers/panels, (1) T panel, (1) LL/LB/LR panel, reducer bushings\*, (1) closure plug and extra hardware
- Ideal for service trucks and reduces inventory




NEC & NEMA 3  
Compliant

U.S. Patent 8,242,386 B1

\* 1/2" trade size does not include reducer bushings.



# TAYMAC® U•CONDUIT – Universal Conduit Body easily configures for all common uses



CATALOG #	DESCRIPTION	VOLUME	PKG. TYPE	STD. PKG.	UPC	1 of 5
<b>U•CONDUIT 10-IN-1 UNIVERSAL CONDUIT BODY</b>						
UCB050	1/2" Universal Conduit Body	5.8 cu in (95 cc)	Shrink Wrap	10	050169571224	50050169571229
UCB075	3/4" Universal Conduit Body	9.5 cu in (156 cc)	Shrink Wrap	10	050169571231	50050169571236
UCB0100	1" Universal Conduit Body	14.3 cu in (234 cc)	Shrink Wrap	10	050169571248	50050169571243

U.S. Patent 8,242,386 B1

[www.Hubbell-RTB.com](http://www.Hubbell-RTB.com)



Locate your local Sales Agent online to request product samples or pricing