

# C Series System

# scalable

# powerful

# flexible



## NEW Keypad Design

From direct customer input, the entire Russound keypad collection is cleaner, simpler and more feature rich. Contemporary blends with interior decor.

SLK1



MDK-C6



Dual gang MDK-C6 keypad adds new features F1 and F2 Favorites accessible on keypad.

SLK1 is a single-gang Decora®-style keypad designed exclusively for the MCA-C3 and MCA-C5 controllers. Conversion kits available in 6 color options.



Works with iPad, iPhone & iPod touch  
Compatible with C-Series controllers.

**My Russound App**



**Bluetooth® Source Kit BSK-1**


Add Bluetooth to any multiroom audio system; powerful range of 50 feet.



**Color Touchscreen TS3**

Dual gang color touchscreen with high-visibility wide angle LCD panel. Convenient control of C-Series sources; installs with a single CAT-5.

**C-Series MCA-C3**



6 source/6 zone controller with built in RDS AM/FM Tuner 20watts x2 per zone. Apple app available for easy wireless control anywhere in the home.



**Digital Media Streamer**

3 Digital streams, AirPlay® enabled plus AM/FM Tuner.

A-K6L



5 Character LCD panel displays source name & volume level.

**Acclaim Thin Bezel Speaker**

A great new look to a great speaker line. Acclaim speakers sport thin bezel with magnetic grills.

Round and square grill options



A-SZ4



Add up to 4 A-BUS subzones to C-Series controllers. Works with all A-BUS keypads (A-K4 and A-K6L).



Visit [www.russound.com](http://www.russound.com) for more detail on the full line of Russound systems and components.





# Series System

superior multiroom  
audio starts here



#### C-Series MCA-C5

8 source/8 zone controller with built in RDS AM/FM tuner 40 watt x 2 channel digital amp zones 1-6. Apple app available for easy wireless control expandable up to 48 zones in the home.

All the power and flexibility you'll ever need are found in Russound "audio everywhere" systems and components. None more exemplary than the C5. Start here and build your customers' dream whole-house solution. Add your choice of kepads and wireless user interface apps. It's all here. Take a look.

## Acclaim Thin Bezel Speakers



#### RSA-61

15° Angled 2-Way Ceiling Speaker

**Recommended Power:**

5-80 Watts

**Tweeter:**

1" Pivoting PEI

**Woofers:**

6 1/2" Vacuum Form Polypropylene



#### RSA-62

15° Angled 2-Way Ceiling Speaker

**Recommended Power:**

5-100 Watts

**Tweeter:**

1" Pivoting Silk - Ferrofluid Cooled

**Woofers:**

6 1/2" IMPP Ribbed Cone



#### RSA-63

15° Angled 2-Way Ceiling Speaker

**Recommended Power:**

5-120 Watts

**Tweeter:**

1" Pivoting Teteron - Ferrofluid Cooled

**Woofers:**

6 1/2" Kevlar



#### RSF-61T

Single-Point, Dual Voice Coil, Twin Tweeter Ceiling Speaker

**Recommended Power:**

5-120 Watts

**Tweeter:**

2 x .75" Pivoting Silk - Ferrofluid cooled

**Woofers:**

6 1/2" IMPP Ribbed Cone



**Round Grill**

3175-534287 RSG-R round



#### RSF-61

2-Way Ceiling Speaker

**Recommended Power:**

5-80 Watts

**Tweeter:**

3/4" Pivoting PEI

**Woofers:**

6 1/2" Vacuum Form Polypropylene



#### RSF-62

2-Way Ceiling Speaker

**Recommended Power:**

5-90 Watts

**Tweeter:**

1" Pivoting Silk - Ferrofluid cooled

**Woofers:**

6 1/2" Polypropylene Cone



#### RSF-63

2-Way Ceiling Speaker

**Recommended Power:**


5-100 Watts

**Tweeter:**

1" Pivoting Silk - Ferrofluid Cooled

**Woofers:**

6 1/2" IMPP Ribbed Cone



#### RSF-64

2-Way Ceiling Speaker

**Recommended Power:**

5-120 Watts

**Tweeter:**

1" Pivoting Teteron - Ferrofluid Cooled

**Woofers:**

6 1/2" Kevlar



**Square Grill**

3175-533990 RSG-S square



audio  
everywhere

2013 Featured Products