

Music Port®

Whatever you want to listen to.

Stream, Sync, Store, and Control.

Deliver four versatile sources through a single component, for easy access to near-limitless audio.



The **Music Port** (NV-MPS4) and **Music Port Elite** (NV-MPS4-E) are masters of audio enjoyment. From one easy-to-operate unit, unleash iTunes and Windows Media Player content, while streaming from favorite online services, for four audio outputs. And the **Elite** takes the luxury of “your music, your way” even further. Enhanced features, such as networked storage and easy integration with Crestron, AMX, and URC systems, offer superior performance.

	4 Sources	Internet Radio	NuVoNet Smart	Auto Sync	Internal Storage	Cloud Sync	Network Storage	IP Control*
Music Port	●	●	●	●	●	●		
Music Port Elite	●	●	●	●	●	●	●	●

*Crestron, AMX, URC Control Compatibility

• 4 Sources

Tune into SiriusXM in the great room while the kids enjoy their own personalized stations on Pandora®. With four simultaneous sources of audio as well, as multiple account support for select services, all from a single unit, everyone, everywhere, has their choice.

• Streaming Internet Radio

Tap directly into the largest portal of music with access to streaming online content from SiriusXM, Pandora, and thousands of online radio stations.

• NuVoNet Smart Source

Browse through your library and select by Artist, Album, Genre, Song and Playlists. All of the metadata from your favorite sources is available on your keypads.

• Auto Sync

Everyone’s own personal collection of music is always available; the Music Port automatically syncs with all network PCs.

• Internal Storage†

Room for thousands of songs on a 320GB hard drive (640GB on *Elite*.)

• Cloud Synchronization

No matter where you are, your music is there too. Your beach house, your boat and your office all sync, so your music, even your latest download, is with you wherever you are.

• Network Storage

Your music should all be in one place, and it is, with this option for expanded storage.

• IP Control

Bring Internet Radio and networked music into your Crestron, AMX or URC system with pre-built control modules.

† NuVo recommends use of MPS4 with libraries of less than 30,000 song files to insure optimum performance

Music Port and Music Port *Elite*.

Specifications

Analog Audio Outputs

Support Audio Formats

Hard Drive Content	MP3, WMA, M4A, WAV, FLAC
Playlist Formats	WPL, M3U, PLS, iTunes
Internet Radio	Pandora, SiriusXM, Rhapsody, TuneIn, Slacker Radio

Support Video Formats

Music Port	HDMI
Music Port Elite	DVI, VGA

System Information

Hard Drive Capacity, Music Pot	320GB (minimum)
Hard Drive Capacity, Music Port Elite	640GB (minimum)
Network Connection	10/100/1000 Mbits/sec
NuVoNet Connection (RJ45)	1

USB Connections

Front Panel	1
Rear Panel	3

Power Requirements

Power Supply	85-265VAC 50/60Hz
Power Consumption	16W

4 RS-232 Serial Connection

NuVo System

Serial Pass Through

RS-232
Male DB-9
57,600 Baud
8 Data Bits
No parity
1 Stop Bit
RS-232
Female DB-9
57,600 Baud
8 Data Bits
No parity
1 Stop Bit

IP Control

Music Port	Windows PC & Mac
	Adobe Flash-Enabled Mobile Devices and Computers
	Apple iPhone, iPod touch
Music Port <i>Elite</i>	AMX
	Crestron
	NuVo
	URC
	Windows PC & Mac
	Adobe Flash-Enabled Mobile Devices and Computers
	Apple iPhone, iPod touch, and iPad*

Physical Specifications

Unit Size (mm)	44 H x 430 W x 250 D
Unit Size (inch)	1 3/4 H x 17 W x 9 7/8 D
Shipping Size (mm)	205 H x 515 W x 343 D
Shipping Size (inch)	8 H x 20 1/4 W x 13 1/2 D
Unit Weight (kg)	2.6
Unit Weight (lbs)	5.75
Shipping Weight (kg)	5.44
Shipping Weight (lbs)	12

NuVo reserves the right to change specifications without notice.