

Face Plates, Rear-Loading



- Designed to flush mount with box eliminator.
- Durable construction.
- Complemented by a broad range of voice/data/video connectors



Features/Benefits


- Provides a rear loading, snap in, flush mounting of Hubbell jacks and AV keystone connectors.
- Available in single and double-gang.
- Individual port configurations allow specification flexibility.
- All IFP plates are supplied with paper labels, clear screw covers, and color-matched screw covers.

Specifications

- ◆ UL listed and cUL certified.
- ◆ ANSI/TIA-606-B station labeling.
- ◆ UL 94V-0 rated flame-retardant material.
- ◆ Mounts to standard NEMA openings and boxes.



IFP Face Plates, Single-Gang




	1-port	2-port	3-port	4-port	6-port
Unit Package	1 per Bag	1 per Bag	1 per Bag	1 per Bag	1 per Bag
Order Qty.	Carton of 25	Carton of 25	Carton of 25	Carton of 25	Carton of 25
Color	Catalog No.	Catalog No.	Catalog No.	Catalog No.	Catalog No.
See Color Code	IFP11XX ✓10G	IFP12XX ✓10G	IFP13XX ✓10G	IFP14XX ✓10G	IFP16XX ✓10G

IFP Face Plates, Double Gang



	6-port	9-port	12-port
Unit Package	1 per Bag	1 per Bag	1 per Bag
Order Qty.	Carton of 10	Carton of 10	Carton of 10
Color	Catalog No.	Catalog No.	Catalog No.
See Color Code	IFP26XX ✓10G	IFP29XX	IFP212XX

Multimedia Wall Plates



Accepts AV and Voice/Data connectors. High impact resistant thermoplastic plate. UL Listed 1863 - Communication Circuit Accessory and CSA Certified. See the Residential Section, page XX for more information.

Standard 1-Gang, 4.625" x 2.875" ✓10G					
Ports	1-port	2-port	3-port	4-port	6-port
See Color Code	NSP11XX	NSP12XX	NSP13XX	NSP14XX	NSP16XX
Standard 2-Gang, 4.625" x 2.875" ✓10G					
Ports	4-port	6-port			
See Color Code	NSP24XX	NSP26XX			
Midsize 1-Gang, 4.875" x 3.125" ✓10G					
Ports	1-port	2-port	3-port	4-port	6-port
See Color Code	NSP101XX	NSP102XX	NSP103XX	NSP104XX	NSP106XX

Blank Wall Plates



Standard, Nylon				
Ports	1-Gang	2-Gang	3-Gang	4-Gang
See Color Code	NP13XX	NP23XX	NP33XX	NP43XX
Mid-Size, Nylon				
Ports	1-Gang	2-Gang		
See Color Code	NPJ13XX	NPJ23XX		

Angled Face Plates, 4-port



Color	Gray	Office White	Telco Ivory	White
Catalog No.	AFP14G ✓10G	AFP14 ✓10G	AFP14I ✓10G	AFP14W ✓10G

XX = Plate Color Options

AL=Almond	BK=Black	EI=Electric Ivory	GY=Gray	LA=Light Almond	OW=Office White	W=White
-----------	----------	-------------------	---------	-----------------	-----------------	---------

