



Selector Switch
Maintained Contact



Selector Switch
Spring Return

Class I, Div. 1 & 2, Groups B,C,D^①
Class I, Zones 1 & 2, Groups IIB, IIA
Class II, Div. 1 & 2, Groups E,F,G
Class III
NEMA 3, 4, 4X, 7(B,C,D) 9(E,F,G)

See Area Classification Chart
page C40 for Details

Listed - File E12379

Certified - File LR11714
See files for details or call Killark.

FEATURES-SPECIFICATIONS

G SELECTOR SWITCH MAINTAINED CONTACT				
CATALOG NUMBER ^①			CONTACT ARRANGEMENT ^②	TYPE OF OPERATION ^③
SHORT ^④	LONG	EXTENDED		
G025-2A3F	G05-2A3F N34	G0L52A3	Left Right	Two position
G025-3C3G	G05-3C3G N34	G0L53C3	Left Center Right	Three position
G025-4H8H	G05-4H8H N34	G0L54H8	1 2 3 4	Four position

G SELECTOR SWITCH MAINTAINED CONTACT WITHOUT CONTACTS				
G025-2A0F	G05-2A0F N34	G0L52A	None	Two position
G025-3C0G	G05-3C0G N34	G0L53C	None	Three position
G025-4H0H	G05-4H0H N34	G0L54H	None	Four position

G SELECTOR SWITCH SPRING RETURN				
G026-3F	G06-3F N34	G0L63	Left Right	Two position spring return to left
G027-6G	G07-6G N34	G0L76	Left Center Right	Three position spring return to center from right or left
G034-6G	G014-6G N34	G0L146	Left Center Right	Three position spring return to center from right, maintain in left
G035-6G	G015-6G N34	G0L156	Left Center Right	Three position spring return to center from left, maintain in right

G SELECTOR SWITCH SPRING RETURN WITHOUT CONTACTS				
G026-0F	G06-0F N34	G0L6	None	Two position spring return to left
G027-0G	G07-0G N34	G0L7	None	Three position spring return to center from right or left
G034-0G	G014-0G N34	G0L14	None	Three position spring return to center from right, maintain in left
G035-0G	G015-0G N34	G0L15	None	Three position spring return to center from left, maintain in right

^① Refer to catalog page C30 to select proper operator for enclosure, C38 & C39 for Accessories, C30 for complete details on Area Classification of operators, C42 for Dimensional Information, C40 for Special Contact Configurations.

^② Nameplates are Double sided. 2 position marked ON-OFF and Blank on other side.

3 position marked HAND-OFF-AUTO and Blank on other side. 4 position is Blank.

^③ Contact Blocks are shown in their normal position.

^④ Short style operators are suitable for Class I Group C & D, Class II Group E,F,G only.

