



- Z-Channel Design Allows Cables to Pass Through Easy Routing
- Quick and Easy Assembly
- Separates and Organizes Cable
- Minimal Packaging Reduces Construction Site Waste

FEATURES

- Rugged construction; Z-frame withstands abuse
- Universal hole pattern on rack uprights mates with other rack/channel models

SPECIFICATIONS

- Channel material:
 - Z-channel: 14ga cold rolled steel
 - C-channel: 16ga cold rolled steel
- Cover material: 16ga cold rolled steel
- Finish: Durable black or aluminum color powder coat

APPROVALS/INSTALLATION

- U.S. Patent No. 6,347,714
- UL Listed File No. E129878
- Packaged to meet Telcordia® GR-63-CORE transportation requirements

APPLICATIONS

- Use in data centers, the equipment room and telecommunications room to provide racking, cable management, grounding and power distribution for network hardware.

Telcordia® is a registered trademark of Telcordia Technologies, Inc.



HUBBELL NEXTFRAME Vertical Cable Management

SteadFast gates
Ensure proper bend radius

Cable management
Organize cable by groups and bundles

Front covers
Conceal cables and easily snap in place

Optional hinged covers
Swing both left and right



Z-Channel Vertical Organizer



C-Channel Vertical Organizer

NEXTFRAME® Vertical Cable Channels are the most durable and easy-to-use channels ever developed.

Hubbell’s innovative design incorporates many patented, labor-saving features that speed assembly and simplify maintenance. Unparalleled durability ensures long-lasting reliability.

Most important, **NEXTFRAME** Vertical Cable Channels protect cable by maintaining the proper bend radius of cables entering and exiting the organizer ensuring maximum cable transmission performance.

VERTICAL ORGANIZERS

Z-Channel, 6" with Cover

Contents:

- VS76(A): 2 Z-channels 38.5" H x 6" W x 10.5" D
2 covers 38.5" W x 6" W
- VS86(A): 1 Z-channel and 1 cover for:
lower, 45.38" H x 6" W x 10.5" D
upper, 38.5" H x 6" W

- 4 gates
- 24 spools
- 4 1/2"-13 x 1" bolts with nuts and washers

Rack Height Inches (mm) Catalog No.

7' (2134) or 7.5' (2286) **VS76***

8' (2438) **VS86***



VS46

Z-Channel, 6" (for Short Racks)

Contents:

- 1 Z-channel 38.5" H x 6" W x 10.5" D
- 16 spools
- 2 1/2"-13 x 1" bolts with nuts and washers

4' (1219) and 5.5' (1676) **VS46***

Z-Channel, 4 1/2" Wide, 0.25" Diameter

Contents:

- 2 Z-channels, 38.50" x 4.5" x 10.5"
- 24 spools
- 4 1/2"-13 x 1" bolts with nuts and washers

7' (2134) **VS74**



VS73

C-Channel, 3 1/4" Wide

Contents:

- 2 C-channels 38.5" H x 3.25" W x 10.5" D
- 24 spools
- 4 1/2"-13 x 1" bolts with nuts and washers

7' (2134) **VS73***

*Product is Black. Add "A" at end of Catalog No. for Aluminum.

VERTICAL ORGANIZERS WITH HINGED COVERS

Contents:

- 2 Z-channels 38.5" H x 12.5" D
- 2 38.5" covers
- 4 hinges and gates
- 24 spools
- 4 1/2"-13 x 1" bolts with nuts and washers

Color	Rack Height In. (mm)	6" Wide Catalog No.	4 1/2" Wide Catalog No.	3 1/4" Wide Catalog No.
Black	7' (2134)	VS76H	VS74H	VS73H

COVERS

Contents: 1 cover

Cover Width	38.5" H Black Catalog No.	45.38" H Black Catalog No.	45.38" H Aluminum Catalog No.
3"	VSC3*	VSC3L	VSC3LA
4"	VSC4	VSC4L	VSC4LA
6"	VSC6*	VSC6L	VSC6LA



VSC6

*Add "A" at end of Catalog Number for Aluminum.

HINGE KIT

Contents:

- 2 hinges and fasteners



Color	Catalog No.
Black	VCKH

Note: Gates not provided; order separately.
Can be used to convert VS76 to VS76H.

JOINING KIT

Contents:

- 1 joining plate
- 4 #12-24 x 5/8" screws, nuts, washers
- 4 1/2"-13 x 1" bolts w/ nuts and washers



Color	Catalog No.
Black	VCJK

VERTICAL RINGS

Contents:

- 2 vertical rings
- 1 mounting kit



MCCVMR2 MCCVMR22

Description	Catalog No.
Bracket, one side	MCCVMR2
Bracket, between racks	MCCVMR22

CABLE MANAGEMENT SPOOLS



Description	Catalog No.
Package of 50 spools, 3", black	ICKSS
Package of 50 spools, 6", black	ICKSS6
Package of 50 spools, 9", black	ICKSS9

GATES

Contents:

- 1 kit of 16 gates

Width	Color	Catalog No.
3.25"	Black	VCG3
4"	Black	VCG4
6"	Black	VCG6

