



FC Duplex, 6-Port
FSPFC6



SC Simplex, 6-Port
FSPSC6



SC/APC Simplex, 6-Port
FSPSCA6



ST Simplex, 6-Port
FSPST6



MPO Simplex, 6-Port
FSPMTPAQ6



Jack-Pack®, 4-Port
FSPHD4X

FC Simplex

Nickle Plate

| Description | Zirconia Ceramic Sleeve |
|------------------|-------------------------|
| FC 6-port (6 FC) | FSPFC6 |
| FC 8-port (8 FC) | FSPFCSS8 |

SC Simplex

Blue

| Description | Phosphor Bronze Sleeve | Zirconia Ceramic Sleeve |
|--------------------|------------------------|-------------------------|
| SC 6-port (6 SC) | FSPSC6 | FSPSCSS6 |
| SC 8-port (8 SC) | FSPSC8 | FSPSCSS8 |
| SC 12-port (12 SC) | FSPSC12 | FSPSCSS12 |

SC Simplex, APC

Green

| Description | Zirconia Ceramic Sleeve |
|------------------|-------------------------|
| SC 6-port (6 SC) | FSPSCA6 |
| SC 8-port (8 SC) | FSPSCA8 |

ST-Style Simplex

Yellow

| Description | Phosphor Bronze Sleeve | Zirconia Ceramic Sleeve |
|-----------------|------------------------|-------------------------|
| ST-style 6-port | FSPST6 | FSPSTSS6 |
| ST-style 8-port | FSPST8 | FSPSTSS8 |

MT-RJ

Black

| Description | Catalog No. |
|--------------|-----------------|
| MT-RJ 6-port | FSPMTRJ6 |
| MT-RJ 8-port | FSPMTRJ8 |

JACK-PACK®, Unloaded

| Description | Catalog No. |
|-----------------|-----------------|
| Keystone 4-port | FSPHD4X |
| Keystone 6-port | FSPHD6X* |

*Will not fit into FTU2 series, FTU4SP or FCR2U9SP enclosures.

MPO, Standard Polarity*

| Color | Application | Simplex 6-Port (72 Fiber) | Duplex 8-Port (96 Fiber) | Duplex 12-Port (144 Fiber) |
|--------|-------------|---------------------------|--------------------------|----------------------------|
| Aqua | OM3/OM4 | FSPMTPAQ6 | FSPMTPDAQ4 | FSPMTPDAQ6 |
| Beige | OM1/OM2 | FSPMTPBE6 | FSPMTPDBE4 | FSPMTPDBE6 |
| Black | Universal | FSPMTPBK6 | FSPMTPDBK4 | FSPMTPDBK6 |
| Green | Singlemode | FSPMTPGN6 | FSPMTPDGN4 | FSPMTPDGN6 |
| Violet | OM4 | FSPMTPVI6 | FSPMTPDVI4 | FSPMTPDVI6 |

*Standard MPO polarity is key-up/key-down. Reversed polarity is key-up/key-up.
Note: Compatible with 12- or 24-fiber MPO connectors.

MPO, Reversed Polarity*

| Color | Simplex 6-Port (72 Fiber) |
|-------|---------------------------|
| Gray | FSPMTPRPGY6 |



Blank Panel
FSPB



SC Simplex, 6-Port
FSPSC6X



SC Simplex, 6-Port
FSPSC8X



SC Duplex, 6-Port
FSPSCD3X



SC Duplex, 12-Port
FSPSCD6X

FSP Adapter Panels, Unloaded

| Description | Catalog No. | Description | Catalog No. |
|----------------------------|-----------------|------------------------|-----------------|
| Blank, snap-in | FSPB | 4 SC duplex or LC quad | FSPSCD4X |
| 6 SC simplex or LC duplex | FSPSC6X | 6 SC duplex or LC quad | FSPSCD6X |
| 8 SC simplex or LC duplex | FSPSC8X | 6 ST-style | FSPST6X |
| 12 SC simplex or LC duplex | FSPSC12X | 8 ST-style | FSPST8X |
| 3 SC duplex or LC quad | FSPSCD3X | 6 MTP-style | FSPSC6X |

Note: Use Hubbell snap mount or screw mount adapters (screws included).