

Preform Grips

SERVICE & DEADEND GRIPS



Service Grips

Cat.No.	Diameter Range	ASCR Std.	Colour Code	Cross Reference	Wt.-lbs./ C	Std. Pkg.	Reference Name
Preforms For Triplex (Service Grip Dead End)- Galvanized Steel (Catalogue number indicates length in inches)							
10SG	.167 - .198	6	Blue	10 GSDE	8	200	10 SSG
13SG	.225 - .257	4	Orange	13 GSDE	13	100	13 SSG
14SG	.258 - .289	2-3	Black	14 GSDE	16	100	14 SSG
15SG	.290 - .325	2	Red	15 GSDE	18	100	15 SSG
19SG	.361 - .400	1/0	Yellow	19 GSDE	38	50	19 SSG
21SG	.401 - .450	2/0	Black	21 GSDE	42	50	21 SSG
23SG	.451 - .510	3/0	Orange	23 GSDE	45	50	23 SSG
26SG	.511 - .580	4/0	Red	26 GSDE	52	50	26 SSG
Preforms For Bare ASCR (Distribution Grip Dead End) - Aluminum (Catalogue number indicates length in inches)							
22DG	.228 - .264	4	Orange Swan	DG 4541	15	50	22 ADN
24DG	.289 - .316	2	Red Sparrow	DG 4542	20	50	24 ADN
28DG	.364 - .398	1/0	Yellow Raven	DG 4544	27	40	28 ADN
31DG	.410 - .447	2/0	Blue Quail	DG 4545	31	30	31 ADN
35DG	.460 - .502	3/0	Orange Pigeon	DG 4546	60	25	35 ADN
37DG	.516 - .563	4/0	Red Penguin	DG 4547	60	25	37 ADN



Uniformed Guy End (Galvanized Steel)

Cat.No.	Diameter	Strength/lbs.	Length	Colour	Std.Pkg.	Wt.-lbs./ C
2514GE	1/4"	6,450	25"	Yellow	60	50
3016GE	5/16"	11,150	30"	Black	40	63
3538GE	3/8"	15,000	35"	Orange	40	106
38716GE	7/16"	20,000	38"	Green	25	175
4512GE	1/2"	26,900	45"	Blue	20	255

Catalogue number indicating length in inches and diameter.



Guy Thimbles: Hot dip Galvanized Steel

Cat.No.	Strand	Std.Pkg.	Wt.-lbs./ C
38GT	3/8"	250	10
12GT	1/2"	250	22
516GT	5/16"	250	24



GRIPS