

Category 6A Shielded System

NEXTSPEED® Shielded Category 6A Jacks

| Unit of Measure | A-Wired | B-Wired |
|-----------------|----------------|----------------|
| 2 per bag | SJ6A2A | SJ6A2B |
| 24 per bag | SJ6A24A | SJ6A24B |



NEXTSPEED® Shielded Patch Panels, Unloaded

| Ports | Height Inches (mm) | Width Inches (mm) | Rack Units | Type | Color | Catalog No. |
|-------|--------------------|-------------------|------------|--------|--------|----------------|
| 24 | 1.75" (45) | 19" (483) | 1 | Flat | Silver | PSJ24S |
| 24 | 1.75" (45) | 19" (483) | 1 | Flat | Black | PSJ24BK |
| 48 | 3.50" (89) | 19" (483) | 2 | Flat | Silver | PSJ48S |
| 48 | 3.50" (89) | 19" (483) | 2 | Flat | Black | PSJ48BK |
| 24 | 1.75" (45) | 19" (483) | 1 | Angled | Black | PSJ24AU |
| 48 | 3.50" (89) | 19" (483) | 2 | Angled | Black | PSJ48AU |



NEXTSPEED® Ascent Shielded Category 6A Patch Cords

| Length | Catalog Number | | | |
|--------|-----------------|----------------|-----------------|----------------|
| | Black | Blue | Gray | Yellow |
| 3' | PC6ABK03 | PC6AB03 | PC6AGY03 | PC6AY03 |
| 5' | PC6ABK05 | PC6AB05 | PC6AGY05 | PC6AY05 |
| 7' | PC6ABK07 | PC6AB07 | PC6AGY07 | PC6AY07 |
| 10' | PC6ABK10 | PC6AB10 | PC6AGY10 | PC6AY10 |
| 15' | PC6ABK15 | PC6AB15 | PC6AGY15 | PC6AY15 |
| 20' | PC6ABK20 | PC6AB20 | PC6AGY20 | PC6AY20 |
| 25' | PC6ABK25 | PC6AB25 | PC6AGY25 | PC6AY25 |

Made-to-order lengths are available from 30ft to 75ft in 5ft increments.
Spec sheets are available for these products online. Type the part number into the search box.



NEXTSPEED® Ascent 10GbE, FTP Cable, 4-Pair

| Color | Plenum Spool | Riser Spool |
|--------|-------------------|--------------------|
| Blue | C6AFTPSPB | C6AFTP SRB |
| Gray | C6AFTPSPGY | C6AFTP SRGY |
| White | C6AFTPSPW | C6AFTP SRW |
| Yellow | C6AFTPSPY | C6AFTP SRY |

Note: All category rated cable is packaged in 1000 foot quantities.

