


# Physical Therapy Areas

Physical therapy centers and spaces provide a variety of treatment options to help patients develop, maintain and restore movement and function. Hubbell has delivery system products including non-metallic multi-service floor boxes that deliver both power and datacom to any point in the room.

## Hubbell SystemOne Floor Boxes and Fire-Rated Poke-Throughs







- Multi-service, multimedia and 4x4 applications
- Subplates accommodate various power and data configurations
- Covers are available in black, gray, brass, aluminum and ivory powder coat finishes



**Modularity and Aesthetics**  
SystemOne is a unique, in-floor delivery system that can be installed in either floor boxes or fire-rated poke-throughs. The system uses a modular approach with over twenty subplates that allow various voice, data and AV connector configurations to fit into each. They can be customized to meet virtually every power and communications application and are easily replaced to accommodate future technology expansion.

Floor Boxes		Fire-Rated Poke-Throughs		Covers		
Description	Cat No.	Description	Factory Assembled Units*	Through Floor Fittings	Description	Type
Cast Iron	<b>S1CFB</b>	(4) 20A; (4) keystone	<b>S1PT4X4xx</b>	<b>S1PT4X4FIT</b>	Cast aluminum	Carpet
Steel	<b>S1SFB</b>	Dual Style Line	<b>S1PTxx</b>	<b>S1PTFIT</b>	Covers	Tile
Steel AV	<b>S1SFBAV</b>	Modular AV	<b>S1PT3IMxx</b>	<b>S1PTAVFIT</b>		
Non-Metallic	<b>S1PFB</b>	Furniture Feed	<b>S1PTFFxx</b>	—		

\* Include through floor fitting, cover and subplate  
For finish options, replace xx: **AL** (Aluminum Finish), **BRS** (Brass Finish), **BL** (Black) or **GY** (Gray)

Subplates		
Description	Description	Description
Style Line® Decorator/GFCI for power and/or datacom applications	Duplex/Duplex for power and/or datacom applications	Duplex/Style Line® Decorator for power and/or datacom applications
 <b>S1SP</b>	 <b>S1SPDU</b>	 <b>S1SPDUSL</b>
(4) 20A and (4) keystone openings. Power can be wired as single or two circuit and isolated ground.	Single Receptacle Opening for 20A-30A Twist-Lock® recep. (1.56" OD) and (2) Keystone openings	Hubbell AV + Power (1) 20A, 125V receptacle and 3 unit recessed iSTATION opening for Data
 <b>S1SP4X4</b>	 <b>S1SPTL</b>	 <b>S1SP3IM</b>

For full offering of SystemOne sub-plates and accessories, please visit our online catalog at [hubbell-wiring.com](http://hubbell-wiring.com).

## Snap Fit Connectors

- Superior performance and signal integrity
- Easily housed in all Hubbell work station and delivery products



F-Type Connectors				
Color	F-Connector, Gold, 3 GHz, Pass-Thru, F/F Coupler	F-Connector, Gold, Pass-Thru, F/F Coupler	F-Connector, Gold, Recessed, Pass-Thru, F/F Coupler	RCA to F-Connector, Gold, Pass-Thru, F/F Coupler
Black	<b>SFF3GBK</b>	<b>SFFGBK</b>	<b>SFGRFBK</b>	<b>SFRFGBK</b>
Office White	<b>SFF3GOW</b>	<b>SFFGOW</b>	<b>SFGRFOW</b>	<b>SFRFGOW</b>
White	<b>SFF3GW</b>	<b>SFFGW</b>	<b>SFGRFW</b>	<b>SFRFGW</b>



## 3.5mm Stereo Jacks

Color	3.5mm to Solder	3.5mm to Screw Terminal	3.5mm to Pass-Thru, F/F Coupler	3.5mm to Pass-Thru, Gold F/F Coupler	3.5mm 110 Termination
Black	<b>SF35SJBK</b>	<b>SF35STBK</b>	<b>SF35FFBK</b>	<b>SF35GFFBK</b>	<b>SF35110BK</b>
Office White	<b>SF35SJOW</b>	<b>SF35STOW</b>	<b>SF35FFOW</b>	<b>SF35GFFOW</b>	—
White	<b>SF35SJW</b>	<b>SF35STW</b>	<b>SF35FFW</b>	<b>SF35GFFW</b>	—



## ISF Series Outlet Frames and Wallplates

Hubbell's nylon plates are virtually unbreakable and UL Listed for power and low-voltage with label fields. The ISF Series frames are available 2-, 3-, 4- and 6-port configurations, as well as various colors and connector configurations.

