

LUMENTASK™ 120V XENON UNDERCABINET

120V Xenon offers rich color and clarity with high intensity, low maintenance Xenon lighting in 5 lengths and 3 finishes. LumenTask undercabinet lighting incorporates a sleek, clean and unobtrusive housing that is home to one of the purest and longest lasting light source - Xenon.

Xenon has a brilliant history in the medical and automotive field where efficiency is key.



120V Xenon Lamp Performance Data


Lamp Life	5,000 Hrs. .
Color Temp.	2,900K



Catalog No.	Lamp	No. of Lamps	Wattage	Length	Finish
X8-120-WH	120V G9 Xenon	1	35W	8"	White
X8-120-BZ	120V G9 Xenon	1	35W	8"	Bronze
X8-120-SS	120V G9 Xenon	1	35W	8"	Stainless Steel
X16-120-WH	120V G9 Xenon	2	2 x 35W	16"	White
X16-120-BZ	120V G9 Xenon	2	2 x 35W	16"	Bronze
X16-120-SS	120V G9 Xenon	2	2 x 35W	16"	Stainless Steel
X24-120-WH	120V G9 Xenon	3	3 x 35W	24"	White
X24-120-BZ	120V G9 Xenon	3	3 x 35W	24"	Bronze
X24-120-SS	120V G9 Xenon	3	3 x 35W	24"	Stainless Steel
X32-120-WH	120V G9 Xenon	4	4 x 35W	32"	White
X32-120-BZ	120V G9 Xenon	4	4 x 35W	32"	Bronze
X32-120-SS	120V G9 Xenon	4	4 x 35W	32"	Stainless Steel
X40-120-WH	120V G9 Xenon	5	5 x 35W	40"	White
X40-120-BZ	120V G9 Xenon	5	5 x 35W	40"	Bronze
X40-120-SS	120V G9 Xenon	5	5 x 35W	40"	Stainless Steel

See page 48 for accessories, replacement lamps and replacement lenses.
Please see pages 49 and 50 for complete specifications.

- Key to LumenTask Diagram:
- 1. Hi-Low-Off switch enables full or 50% lighting level.
 - 2. Tempered frosted, prismatic glass lens that slides in for easy installation.
 - 3. Xenon lamp with anodized aluminum reflector.




LUMENTASK™ ACCESSORIES FOR LED and XENON MODELS

Key to Connector Diagrams

- 1. EZ-1 connects two LumenTask™ fixtures in series.
- 2. EZ Connectors connects two LumenTask™ fixtures with a flexible cord:
 - EZ-3 (3" connector)
 - EZ-6 (6" connector)
 - EZ-12 (12" connector)
 - EZ-18 (18" connector)
- 3. JB-1 junction box.
5"L x 1-1/2"H x 2-1/2"W
- 4. CP-6 72" cord and plug.

NOTE: EZ Connectors, JB-1 and CP-6 are available in white only.



Catalog No.	Description
EZ-1	Connects two LumenTask fixtures directly together
EZ-3	3" flexible LumenTask fixture to fixture connector
EZ-6	6" flexible LumenTask fixture to fixture connector
EZ-12	12" flexible LumenTask fixture to fixture connector
EZ-18	18" flexible LumenTask fixture to fixture connector
JB-1	LumenTask Junction Box for hardwire installation
CP-6	72" cord and plug with modular connector
G9-120VCL	35W Xenon replacement lamp for 120V LumenTask. G9 base. Clear
GL8	8" replacement lens for 8" LumenTask models
GL16	16" replacement lens for 16" LumenTask models
GL24	24" replacement lens for 24" LumenTask models
GL32	32" replacement lens for 32" LumenTask models