

## LUMENTASK™ 120V XENON UNDERCABINET

120V Xenon offers rich color and clarity with high intensity, low maintenance Xenon lighting in 5 lengths and 3 finishes. LumenTask undercabinet lighting incorporates a sleek, clean and unobtrusive housing that is home to one of the purest and longest lasting light source - Xenon.

Xenon has a brilliant history in the medical and automotive field where efficiency is key.

**X32-120-WH**

### 120V Xenon Lamp Performance Data

<b>Lamp Life</b>	5,000 Hrs. .
<b>Color Temp.</b>	2,900K



Catalog No.	Lamp	No. of Lamps	Wattage	Length	Finish
<b>X8-120-WH</b>	120V G9 Xenon	1	35W	8"	White
<b>X8-120-BZ</b>	120V G9 Xenon	1	35W	8"	Bronze
<b>X8-120-SS</b>	120V G9 Xenon	1	35W	8"	Stainless Steel
<b>X16-120-WH</b>	120V G9 Xenon	2	2 x 35W	16"	White
<b>X16-120-BZ</b>	120V G9 Xenon	2	2 x 35W	16"	Bronze
<b>X16-120-SS</b>	120V G9 Xenon	2	2 x 35W	16"	Stainless Steel
<b>X24-120-WH</b>	120V G9 Xenon	3	3 x 35W	24"	White
<b>X24-120-BZ</b>	120V G9 Xenon	3	3 x 35W	24"	Bronze
<b>X24-120-SS</b>	120V G9 Xenon	3	3 x 35W	24"	Stainless Steel
<b>X32-120-WH</b>	120V G9 Xenon	4	4 x 35W	32"	White
<b>X32-120-BZ</b>	120V G9 Xenon	4	4 x 35W	32"	Bronze
<b>X32-120-SS</b>	120V G9 Xenon	4	4 x 35W	32"	Stainless Steel
<b>X40-120-WH</b>	120V G9 Xenon	5	5 x 35W	40"	White
<b>X40-120-BZ</b>	120V G9 Xenon	5	5 x 35W	40"	Bronze
<b>X40-120-SS</b>	120V G9 Xenon	5	5 x 35W	40"	Stainless Steel

See page 48 for accessories, replacement lamps and replacement lenses. Please see pages 49 and 50 for complete specifications.

#### Key to LumenTask Diagram:

1. Hi-Low-Off switch enables full or 50% lighting level.
2. Tempered frosted, prismatic glass lens that slides in for easy installation.
3. Xenon lamp with anodized aluminum reflector.

