

PRODUCT INFORMATION

Hi-Pro LED

High lumen, omni-directional lamps for industrial and commercial applications

Features

- Replaces HID, CFL, and Incandescent
- Direct wire range voltage 100-277V
- Approved for totally enclosed fixtures
- IP65 rated
- 3 CCT options
- Base up, base down or horizontal operation
- 5 Year limited warranty



S9397



High Lumen Industrial/Commercial LED Lamps

Item Number	Lamp Description	Replaces INC/CFL/HID	W	V	Base Type	CCT	Lm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack/Mstr.
S9670	18W/LED/HID/2700K/100-277V	120/32/70	18	100-277	E26	2700K	2070	6 7/8	50K	045923096709	48
S9390	18W/LED/HID/5000K/100-277V	120/32/70	18	100-277	E26	5000K	2160	6 7/8	50K	045923093906	48
S9678	18W/LED/HID/AMBER/100-277V	—	18	100-277	E26	Amber	—	6 7/8	50K	045923096785	48
S9671	22W/LED/HID/2700K/100-277V	150/40/100	22	100-277	E26	2700K	2530	7 11/16	50K	045923096716	48
S9391	22W/LED/HID/5000K/100-277V	150/40/100	22	100-277	E26	5000K	2640	7 11/16	50K	045923093913	48
S9672	36W/LED/HID/2700K/100-277V	200/55/150	36	100-277	E26	2700K	4140	9 1/4	50K	045923096723	12
S9392	36W/LED/HID/5000K/100-277V	200/55/150	36	100-277	E26	5000K	4320	9 1/4	50K	045923093920	12
S9673*	45W/LED/HID/4000K/120-277V	300/65/175	45	100-277	EX39	4000K	5400	10 3/4	50K	045923096730	12
S9393*	45W/LED/HID/5000K/100-277V	300/65/175	45	100-277	EX39	5000K	5400	10 3/4	50K	045923093937	12
S9674*	54W/LED/HID/4000K/120-277V	300/85/250	54	100-277	EX39	4000K	6480	10 3/4	50K	045923096747	12
S9394*	54W/LED/HID/5000K/100-277V	300/85/250	54	100-277	EX39	5000K	6480	10 3/4	50K	045923093944	12
S9675*	80W/LED/HID/4000K/120-277V	400/100/320	80	100-277	EX39	4000K	9600	9 1/4	50K	045923096754	6
S9395*	80W/LED/HID/5000K/100-277V	400/100/320	80	100-277	EX39	5000K	9600	9 1/4	50K	045923093951	6
S9676*	100W/LED/HID/4000K/100-277V	500/150/400	100	100-277	EX39	4000K	12000	9 5/8	50K	045923096761	6
S9396*	100W/LED/HID/5000K/100-277V	500/150/400	100	100-277	EX39	5000K	12000	9 5/8	50K	045923093968	6
S9677*	120W/LED/HID/4000K/100-277V	750/200/600	120	100-277	EX39	4000K	14400	10 3/8	50K	045923096778	6
S9397*	120W/LED/HID/5000K/100-277V	750/200/600	120	100-277	EX39	5000K	14400	10 3/8	50K	045923093975	6

Accessories

92-406	Mog to Med Socket Reducer for S9390, S9391, S9392, S9670, S9671, S9672 and S9678	045923924064
80-929	Hard Wire Surge Protector	045923809293