



IFP Face Plates, with Label Fields, 1- and 2-Gang



Color	1-Gang					2-Gang		
	1-Port	2-Port	3-Port	4-Port	6-Port	6-Port	9-Port	12-Port
Almond	IFP11AL	IFP12AL	IFP13AL	IFP14AL	IFP16AL	IFP26AL	-	-
Black	IFP11BK	IFP12BK	IFP13BK	IFP14BK	IFP16BK	IFP26BK	IFP29BK	IFP212BK
Gray	IFP11GY	IFP12GY	IFP13GY	IFP14GY	IFP16GY	IFP26GY	IFP29GY	IFP212GY
Ivory	IFP11EI	IFP12EI	IFP13EI	IFP14EI	IFP16EI	IFP26EI	IFP29EI	IFP212EI
Light Almond*	IFP11LA	IFP12LA	IFP13LA	IFP14LA	IFP16LA	IFP26LA	IFP29LA	IFP212LA
Office White	IFP11OW	IFP12OW	IFP13OW	IFP14OW	IFP16OW	IFP26OW	IFP29OW	IFP212OW
White	IFP11W	IFP12W	IFP13W	IFP14W	IFP16W	IFP26W	IFP29W	IFP212W

Note: *Light Almond plates match Office White non-metallic raceway, boxes, jacks and connectors.

Stainless Steel Face Plates without Label Fields, 1- and 2-Gang



Catalog No.	1-Gang					2-Gang			
	1-Port	2-Port	3-Port	4-Port	6-Port	4-Port	6-Port	9-Port	12-Port
	SSF11	SSF12	SSF13	SSF14	SSF16	SSF204	SSF206	SSF209	SSF212

Stainless Steel Face Plates with Label Fields

1-Gang	Catalog Number
1-Port	SSFL11
2-Port	SSFL12
3-Port	SSFL13
4-Port	SSFL14
6-Port	SSFL16

Duplex and Decorator Plates with Label Fields

	Color	Duplex Plate	Decorator Plate
	Almond	IFP18AL	IFP126AL
	Office White	IFP18OW	IFP126OW

Standard Duplex and Decorator Plates with No Label Fields, 1- and 2-Gang

	Color	1-Gang Duplex Plate	1-Gang Decorator Plate	2-Gang Decorator Plate
	Almond	NP8AL	NP26AL	NP262AL
	Black	NP8BK	NP26BK	NP262BK
	Ivory	NP8I	NP26I	NP262I
	Gray	NP8GY	NP26GY	NP262GY
	Light Almond*	NP8LA	NP26LA	NP262LA
	White	NP8W	NP26W	NP262W

Note: *Light Almond plates match Office White non-metallic raceway, boxes, jacks and connectors.

630 Wall Phone Plates, 1-Gang


Stainless Steel, 1-Gang wall phone plate.



P630S1GJ6 **P630SR1GJ6**

Jack Format	Includes Gray Jack	Catalog Number
Flush	6-position USOC, RJ25	P630S1GJ6
Flush	8-position Cat. 5e, RJ45	P630S1GJ8
Recessed	6-position USOC, RJ25	P630SR1GJ6
Recessed	8-position Cat. 5e, RJ45	P630SR1GJ8

Keystone Opening
 Hole size for mounting all Hubbell Jacks.





HDMI** Decorator Frames



Color	1-Port	2-Port
Black	NS801BK	NS802BK
Gray	NS801GY	NS802GY
Ivory	NS801I	NS802I
Light Almond	NS801LA	NS802LA
White	NS801W	NS802W

Note: **HDMI (High Definition Media Interface).

Blank Duplex Outlet Frames, 1-Gang



Color	Keystone 2-Port	Keystone 4-Port
Almond	BR106AL	Q106AL
Black	BR106B	Q106B
Gray	BR106G	Q106G
Ivory	BR106E	Q106E
Light Almond*	BR106LA	Q106LA
Office White	BR106C	Q106O
White	BR106W	Q106W

Note: *Light Almond frames match Office White non-metallic raceway, boxes, jacks and connectors.

Blank Decorator Outlet Frames, 1-Gang



Color	Keystone 2-Port	Keystone 3-Port	Keystone 4-Port	Keystone 6-Port	HD15/9 or HDMI	(2) HD15/9 or HDMI	(1) Recessed HD15/9 or HDMI	.406 in. (10.3) hole	Blank
Almond	ISF2AL	ISF3AL	ISF4AL	ISF6AL	ISFB15AL	—	—	NS621AL	NS620AL
Black	ISF2BK	ISF3BK	ISF4BK	ISF6BK	ISFB15BK	ISFB215BK	ISFBR15BK	—	—
Gray	ISF2GY	ISF3GY	ISF4GY	ISF6GY	ISFB15GY	ISFB215GY	ISFBR15GY	—	—
Ivory	ISF2EI	ISF3EI	ISF4EI	ISF6EI	ISFB15EI	ISFB215EI	ISFBR15EI	NS621I	NS620I
Light Almond*	—	—	—	—	ISFB15LA	—	—	NS621LA	NS620LA
Office White	ISF2OW	ISF3OW	ISF4OW	ISF6OW	ISFB15OW	ISFB215OW	ISFBR15OW	—	—
White	ISF2W	ISF3W	ISF4W	ISF6W	ISFB15W	ISFB215W	ISFBR15W	NS621W	NS620W

Note: *Light Almond frames match Office White non-metallic raceway, boxes, jacks and connectors.

Secure-IT Plates



Secure-IT Plates protect mated and unmated connections from physical damage and unauthorized tampering. Available in Tamper-Resistant and Weatherproof versions.



TPF1W

Tamper-Resistant Plates

Color	1-Gang/4-Port Catalog Number
Black	TPF1BK
Gray	TPF1GY
Office White	TPF1OW
White	TPF1W



TWPF1GY

NEMA 3R Weatherproof Plates

Color	1-Gang/4-Port Catalog Number
Gray	TWPF1GY



HDMI Connectors



HDMI Feed Thru Coupler

Description	Catalog Number
Single	HDMIC14



Keystone HDMI Feed Thru

Description	Color	Catalog Number
Single	Black	SFHC14BK
Single	White	SFHC14W



HDMI Feed Thru 3-Inch Tail

Description	Catalog Number
Single	HDMIT14

DVI Adapters/Couplers



DVI-I Coupler

Description	Catalog Number
Single	DVI1



DVI to VGA Adapter

Description	Catalog Number
Single	DVI151



DVI to HDMI Adapter

Description	Catalog Number
Single	DVIHDMI1



DVI to HDMI Adapter

Description	Catalog Number
Single	HDMIC1

110 Audio Video Modules*

Description	Housing Color	Catalog Number
RCA Component, Video to 110 Termination, 1 Unit, 75 ft. max. HD Cat 5, 5e, 6 UTP	Almond Black Ivory Gray Office White White	IMCR1101AL IMCR1101BK IMCR1101EI IMCR1101GY IMCR1101OW IMCR1101W
S-Video, Stereo RCA Audio to 110 Termination, 1 Unit, 100 ft. max. Cat 5, 5e, 6 UTP	Almond Black Ivory Gray Office White White	IMSR1101AL IMSR1101BK IMSR1101EI IMSR1101GY IMSR1101OW IMSR1101W
S-Video, 3.5mm Stereo Jack to 110 Termination, 1 Unit, 100 ft. max. Cat 5, 5e, 6	Almond Black Ivory Gray Office White White	IMSV351101AL IMSV351101BK IMSV351101EI IMSV351101GY IMSV351101OW IMSV351101W
RCA Composite, Video, Stereo Audio to 110 Termination, 1 Unit, 100 ft. max. Cat 5, 5e, 6	Almond Black Ivory Gray Office White White	IMR1101AL IMR1101BK IMR1101EI IMR1101GY IMR1101OW IMR1101W
Stereo RCA, Audio 110 Termination, 1 Unit, 100 ft. max. Cat 5, 5e, 6	Almond Black Ivory Gray Office White White	IMAR1101AL IMAR1101BK IMAR1101EI IMAR1101GY IMAR1101OW IMAR1101W

Note: *Not UL Listed.



IMCR1101W



IMSR1101W



IMSV351101W



IMR1101W



IMAR1101W



IMCRS15OW



IMCRS10W



IM3RS10W



IMRSJ10W



IMCRF10W



IM3RF10W



IMSP10W



SPPBK10

SPPR10

110 Audio Video Modules

Description	Housing Color	Catalog Number
RCA Component Video,* Audio 110 Termination, 1.5 Unit	Almond	IMCRS15AL
	Black	IMCRS15BK
	Ivory	IMCRS15EI
	Gray	IMCRS15GY
	Office White	IMCRS15OW
	White	IMCRS15W
RCA Component* Video, Solder, 1 Unit	Almond	IMCRS1AL
	Black	IMCRS1BK
	Ivory	IMCRS1EI
	Gray	IMCRS1GY
	Office White	IMCRS1OW
	White	IMCRS1W
RCA Composite, Video Audio, Solder, 1 Unit	Almond	IM3RS1AL
	Black	IM3RS1BK
	Ivory	IM3RS1EI
	Gray	IM3RS1GY
	Office White	IM3RS1OW
	White	IM3RS1W
RCA Composite, Video, 3.5mm Stereo Jack, Solder, 1 Unit	Almond	IMRSJ1AL
	Black	IMRSJ1BK
	Ivory	IMRSJ1EI
	Gray	IMRSJ1GY
	Office White	IMRSJ1OW
	White	IMRSJ1W

Gold Feed-Through Audio Video RCA Couplers

Description	Housing Color	Catalog Number
RCA Component* Video, Gold, Pass-Through, F/F Coupler, 1 Unit	Almond	IMCRF1AL
	Black	IMCRF1BK
	Ivory	IMCRF1EI
	Gray	IMCRF1GY
	Office White	IMCRF1OW
	White	IMCRF1W
RCA Composite, Video Audio, Gold, Pass-Through, F/F Coupler, 1 Unit	Almond	IM3RF1AL
	Black	IM3RF1BK
	Ivory	IM3RF1EI
	Gray	IM3RF1GY
	Office White	IM3RF1OW
	White	IM3RF1W

Gold Speaker Posts and Banana Plugs


Description	Housing Color	Catalog Number
Speaker Post, Gold, Black and Red, Screw Termination	Almond	IMSP1AL
	Black	IMSP1BK
	Ivory	IMSP1EI
	Gray	IMSP1GY
	Office White	IMSP1OW
	White	IMSP1W
Speaker Banana Plugs*, Gold, Screw Termination, 10-Packs	Black	SPPBK10
	Red	SPPR10

Note: *Not UL Listed.



Modular Face Plate Frames

Color	1-Gang	2-Gang
Almond	IMF1AL	IMF2AL
Black	IMF1BK	IMF2BK
Gray	IMF1GY	IMF2GY
Ivory	IMF1EI	IMF2EI
Office White	IMF1OW	IMF2OW
White	IMF1W	IMF2W



Raceway Bezel Frames*

Color	1-Gang
Almond	KPIMBZAL
Gray	KPIMBZGY
Office White	KPIMBZOW



Unloaded Keystone Modules

Color	1-Port, Flat 1 Unit	2-Port, Flat 1 Unit	1-Port, Angled 1.5 Unit	2-Port, Angled 1.5 Unit	Recessed Angle 1-Port, 1.5 Unit	Recessed Angle 2-Port, 1.5 Unit
Almond	IM1K1AL	IM2K1AL	IM1KA15AL	IM2KA15AL	-	-
Black	IM1K1BK	IM2K1BK	IM1KA15BK	IM2KA15BK	IM1IA15BK	IM2IA15BK
Ivory	IM1K1EI	IM2K1EI	IM1KA15EI	IM2KA15EI	IM1IA15EI	IM2IA15EI
Gray	IM1K1GY	IM2K1GY	IM1KA15GY	IM2KA15GY	IM1IA15GY	IM2IA15GY
Office White	IM1K1OW	IM2K1OW	IM1KA15OW	IM2KA15OW	IM1IA15OW	IM2IA15OW
White	IM1K1W	IM2K1W	IM1KA15W	IM2KA15W	IM1IA15W	IM2IA15W

Color	Blank 0.5 Unit	Blank 1 Unit	Blank 1.5 Unit	SC Angled 1-Port, 1.5 Unit	SC Angled 2-Port, 1.5 Unit
Almond	IMB05AL	IMB1AL	IMB15AL	-	-
Black	IMB05BK	IMB1BK	IMB15BK	IM1SCA15BK	IM2SCA2BK
Ivory	IMB05EI	IMB1EI	IMB15EI	IM1SCA15EI	IM2SCA2EI
Gray	IMB05GY	IMB1GY	IMB15GY	IM1SCA15GY	IM2SCA2GY
Office White	IMB05OW	IMB1OW	IMB15OW	IM1SCA15OW	IM2SCA2OW
White	IMB05W	IMB1W	IMB15W	IM1SCA15W	IM2SCA2W

HD (High Definition) 15-Pin/9-Pin Modules

	Blank HD15/9 or HDMI Module, 1 Unit	IMBDS1xx	10-Pack
	Blank HD15/9 or HDMI Module, 1.5 Unit	IMBDSA15xx	1-Pack

DVI Modules

	DVI Blank, Unloaded, 1.5 Unit	IMBDVI15xx	1-Pack
		IMBDVI1015xx	10-Pack

Note: xx = Color: **AL** (Almond), **BK** (Black), **EI** (Ivory), **GY** (Gray), **LA** (Light Almond), **OW** (Office White), and **W** (White).

Hubbell iSTATION Audio/Video Modules

XLR, speakON® and ¼ inch modules applications include video distribution, desktop and laptop computers, monitors, cameras, microphones and projectors, home theater and entertainment. Note: Order IMAVB15 series blank modules with AV connectors for Hubbell iSTATION applications.

	AV Blank 1.5 Unit	IMAVB15xx*	10-Pack
	XLR Screw Terminal	XLRST10	
	XLR Solder-Type	XLR10	
	speakON® Conn. Solder-Type	SC10	
	USB Feed-Thru A-to-B	USB10	
	¼" Stereo Jack Solder-Type	14S10	

Note: xx = Color: **AL** (Almond), **BK** (Black), **EI** (Ivory), **GY** (Gray), **LA** (Light Almond), **OW** (Office White), and **W** (White).


*Not UL Listed.

speakON® is a registered trademark of Neutrik® AG.



Specifications

- Low-profile design.
- Accepts XJ jacks, audio video and fiber connectors.
- Provided with double-sided tape and mounting screws for easy installation.
- UL and cUL listed.
- Constructed with a high-impact resistant, flame-retardant polymer.
- ANSI/TIA-606B compliant.



ISB120W



ISB10W



ISB20W



ISB40W



ISB60W



ISB120W

ISB Surface Mount Boxes, 1- and 2-Port

Ideal for open office, compact surface mount environments, and retrofits to support data, voice, and multimedia applications. Can be mounted with supplied surface mounting screws or double-sided adhesive tape.

Color	1-Port Catalog Number	2-Port Catalog Number
Ivory	ISB1EI	ISB2EI
Office White	ISB10W	ISB20W
White	ISB1W	ISB2W

ISB Surface Mount Boxes, 4- and 6-Port

Ideal for open office MUTOA cabling, compact surface mount environments, and retrofits to support data, voice, and multimedia applications. Features adjustable furniture latches to provide an additional mounting option to common ANSI/TIA/EIA standard furniture openings, and solutions requiring fiber. Box bases feature fiber storage posts that can store one meter fiber cable after termination.

Color	4-Port Catalog Number	6-Port Catalog Number
Ivory	ISB4EI	ISB6EI
Office White	ISB40W	ISB60W
White	ISB4W	ISB6W

ISB Surface Mount Boxes, 12-Port

Ideal for open office MUTOA cabling, large capacity surface mount applications and retrofits to support data, voice, and multimedia installations. Can be mounted with supplied surface mounting screws or double-sided adhesive tape and mounted to NEMA electric boxes or relay racks.

Color	12-Port Catalog Number
Ivory	ISB12EI
Office White	ISB120W
White	ISB12W