




Weatherproof FS Boxes

One-piece construction electrical box provides a clean, weatherproof, UL Listed installation. Deep design for GFCIs. Paintable. UV rated plastic for long outdoor life.




| CATALOG NUMBER | UPC/DCI/NAED MFG #01 8997 | SIDING TYPE/STYLE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|---------------------------|-------------------|----------|---------|-------|-------|-------|
| FS8141 | 17340 | 1/2" Lap | 25 | 25 | 5.093 | 3.312 | 2.056 |
| FS8151 | 17341 | 5/8" Lap | 25 | 25 | 5.093 | 3.312 | 2.056 |
| FS8161 | 17342 | Flat Surfaces | 25 | 25 | 5.093 | 3.312 | 2.056 |
| FS8171 | 17343 | Dutch Lap | 25 | 25 | 5.093 | 3.312 | 2.056 |

Add suffix "GC" to Catalog # when ordering in Canada, for example FS8141GC.
PATENTED.



Features and Benefits

- Provides a solid, attractive, UL Listed installation
- Accommodates GFCI, switches, and outlets
- For use with all siding types...1/2", 5/8", dutch lap, and flat surfaces



Installation Instructions



Remove KO from FS Box and insert NM cable connector. Push cable through connector and position box onto siding.



Mount box to siding and install your choice of either a GFCI, Switch or Duplex receptacle.

Complete installation with code required weatherproof while-in-use cover.

Non-Metallic Fixture Box for Stone or Brick

Adjustable depth fixture box for new stone or brick. Adjusts to fit an exterior wall finish from 1-1/2" to 5" thick. Color: Paintable white face plate. Face plate is UV rated plastic for long outdoor life.



IN for Brick

| CATALOG NUMBER | UPC/DCI/NAED MFG #01 8997 | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|---------------------------|----------|---------|-------|--------|-------|
| 8141ALP | 10767 | 1 | 1 | 6.625 | 10.200 | 6.750 |

Add suffix "GC" to Catalog # when ordering in Canada, for example 8141ALPGC.
PATENT PENDING.



Features and Benefits

- Installation is fast and easy – it looks great too
- Versatile depth adjustment for 1-1/2" to 5" thick stone or brick exterior wall finishes
- Textured, paintable face plate
- For fixtures up to 10 lbs.
- Includes box, flange, face plate, (4) #6 x 1/2" screws, (4) #8 x 1-1/4" screws, and an NM94 cable connector.

