

# Lifetime Plus® Super Flex® Lighted Extension Cords

3-Conductor Grounded • Type SJTW • -50°C to 60°C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	TYPE	POWER RATING			PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
						VOLTS	AMPS	WATTS				
03387.63.05	3	16	25	Yellow	SJTW	125	13	1625	12	1.7	20	079407033874
03390.63.05	3	14	25	Yellow	SJTW	125	15	1875	12	2.5	30	079407033904
03391.63.05	3	14	50	Yellow	SJTW	125	15	1875	6	4.7	28	079407033911
03392.63.05	3	14	100	Yellow	SJTW	125	13	1625	4	9.2	37	079407033928
03397.61.05	3	12	25	Yellow	SJTW	125	15	1875	6	3.7	22	079407033973
03398.61.05	3	12	50	Yellow	SJTW	125	15	1875	4	7.0	28	079407033980
03399.61.05	3	12	100	Yellow	SJTW	125	15	1875	2	13.1	26	079407033997
03350.63.05	3	12	2	Yellow	SJTW	125	15	1875	6	1.0	6	079407033508
03351.61.05	3	12	25	Yellow	SJTW	125	15	1875	6	4.2	25	079407416592
03352.61.05	3	12	50	Yellow	SJTW	125	15	1875	4	7.5	30	079407416608
03353.61.05	3	12	100	Yellow	SJTW	125	15	1875	2	13.6	27	079407416615



## Product Description:

Lifetime Plus® Super Flex® extension cords have a connector end that lights up to indicate the power is on. Twice as flexible as other extension cords, the high-visibility yellow cord resists moisture and will not crack in arctic cold or melt in desert heat. The super-tough jacket provides extra resistance to cracking and abrasion. The Lifetime Plus extension cords have a limited lifetime warranty and remain flexible to -40°C.

## Product Construction:

### Conductor:

- 16 AWG, 14 AWG or 12 AWG stranded bare copper per ASTM B174

### Insulation:

- Premium-grade, color-coded PVC

### Jacket:

- PVC; yellow
- Temperature range: -40°C to 60°C
- Voltage rating: 300 volts

### NEMA Configuration:

- 5-15P/5-15R

## Applications:

- Chain saws
- Wet/dry vacs
- Orbital sanders
- Other outdoor equipment

## Features:

- Lights up with power
- Super-flexible
- Weather- and water-resistant
- Limited lifetime warranty
- 3-conductor grounded

## Industry Approvals:

- UL Listed
- OSHA Acceptable

**CAROL BRAND**



OSHA Acceptable  
Occupational Safety and Health  
Administration

**General Cable**