Component Specifications

QuickPort® Patch Block - Field Configurable

APPLICATION

For wall-mount applications requiring a compact cross-connect block with a small number of field configurable ports. Leviton's QuickPort Patch Block holds up to twelve connectors. Useful where low cost, add-as-you-go flexibility is desired.

FEATURES

- Compatible with Leviton QuickPort snap-in connectors and blanks
- White write-on blocks for port identification
- · Includes four blanks (color: black)

STANDARDS COMPLIANCE

- Meets or exceeds all applicable standards
- UL Listed
- CSA Certified
- Complies with TIA/EIA-568-A
- Meets FCC Part 68

PHYSICAL SPECIFICATIONS

Materials: Panels are 14 gauge steel, painted black.

Plastic connector housings are black fire-retardant plastic rated UL 94V-0, with

white write-on blocks.

Capacity: 12-Port

Dimensions: 10.0"H x 2.30"W x .45"D

DESIGN CONSIDERATIONS

- Verify cable pathway in closet
- Recommend that blocks be arranged to allow for future growth
- Port ID can be achieved by several options: Using write-on fields; using Leviton's LabelWare™ System; or using different connector colors to color-code the ports
- 89-D mounting bracket (40089-00D) and QuickPort snap-in connectors are sold separately
- Four blanks are included (color: black)



Pictured: QuickPort 12-Port Patch Block (mounting bracket and connectors sold separately)

WARRANTY INFORMATION

For a copy of Leviton product warranties, log on to www.levitonvoicedata.com/warranty.

TYPICAL SPECIFICATION

The patch block shall provide 12 ports that can be configured and/or changed individually, and accept QuickPort connectors. The patch block material shall be 14-gauge steel with a black powder coat. All plastic parts shall be high-impact fire-retardant plastic rated UL94V-0. The patch block shall include write-on label strips and be wall-mountable on an industry standard 89-D bracket. Colors and configurations to be specified per schedule on plan.

ELECTRONIC FILES

For CAD files, Typical Specs, or Dimensional Line Art (.DXF, .DWG, MS-DOS.eps or .TXT), log on to www.levitonvoicedata.com.



For Technical Support Call 1-425-485-4288; in USA call 1-800-824-3005. Spec sheets and updates are also available at www.levitonvoicedata.com.




QuickPort® Patch Block - Field Configurable


Part Numbers 49255-Q89 40089-00D

DIMENSIONAL LINE ART

For Dimensional Line Art (.DXF, .DWG, MS-DOS.eps or .TXT), log on to www.levitonvoicedata.com.







89D Mounting Bracket (Available separately)

PART NUMBERS

Description	Part No.
QuickPort 12-Port Patch Block	49255-Q89
QuickPort Patch Block 89D mounting bracket (available separately)	40089-00D





For Technical Support Call 1-425-485-4288; in USA call 1-800-824-3005. Spec sheets and updates are also available at www.levitonvoicedata.com.

2222 – 222nd St. SE • Bothell, WA 98021 USA • Tel: 1-800-722-2082 / 1-425-485-4288 • Fax: 1-425-483-5270 • Int'l Fax: 1-425-485-9170 • GSA Schedule Available.