

## Data T<sup>®</sup>-Cutter Wire Cutters



- Cuts round communication cable and maintains cable geometry for better cable performance
- Cuts multi-pair cable up to .500 in. (12.7mm) and coaxial cable up to RG-9/U
- Suitable for soft cables (not ACSR)
- Steel reinforced center conductors can be trimmed with bolt cutting holes
- Cushioned comfort grip handles
- Locking latch keeps tool closed in pouch
- Data T<sup>®</sup>-Cutter II designed for RG-58 and RG-6 coaxial cable

| Description                    | Cat. No. |
|--------------------------------|----------|
| Data T <sup>®</sup> -Cutter    | 45-074   |
| Data T <sup>®</sup> -Cutter II | 45-075   |

## Combo Tool

- Convenient, four-function tool features precision-ground stripping holes and knife-to-anvil cutting blades
- Crimps bare and insulated terminals
- Strips 8 – 20 AWG solid and 10 – 22 AWG stranded wire
- Cuts unhardened bolts (4-40, 6-32, 8-32, 10-24 and 10-32) and reforms threads



| Description | Cat. No. |
|-------------|----------|
| Combo Tool  | 30-428   |

## Multi-Crimp Strip Tool


- Cuts wire
- Crimps insulated and non-insulated wires
- Cuts bolts
- Strips 10-22 AWG wire



| Description            | Cat. No. |
|------------------------|----------|
| Multi-Crimp Strip Tool | 45-778   |

## T<sup>®</sup>-Cutter Wire Cutters

- Hardened steel, shear-type blades
- Spring-loaded automatic opening
- Convenient plier nose for extra gripping strength
- Corrosion-resistant, black oxide finish
- Tough steel construction
- Locking tab keeps spring in place



| Description  | Wire Range  | Cat. No. |
|--|---|----------|
| T <sup>®</sup> -Cutter Wire Cutter                 | Up to 1/2 in. O.D. fine-stranded wire and 10 AWG solid wire | 45-123   |
| Reflex™ Premium T <sup>®</sup> -Cutter Wire Cutter | Up to 1/2 in. O.D. fine-stranded wire and 10 AWG solid wire | 45-423   |

## T<sup>®</sup>-Cutter Lite Wire Cutter

In today's cutting-edge electronic production and assembly operations, the T<sup>®</sup>-Cutter Lite is a "must-have." Stranded or solid, copper or aluminum, this wire cutter cuts cleanly and accurately. Compact and lightweight with a cushioned ESD grip prove comfort and precision go hand-in-hand.

- Knife-type blade provides a shear-type cut
- Lightweight, compact design
- Perfect for copper and aluminum wire
- Cushioned ESD grip



| Description                             | Cat. No. |
|---|----------|
| T <sup>®</sup> -Cutter Lite Wire Cutter | 45-260   |

## Coax Strip and Crimp Tool

- Precision, form-ground stripping holes remove outer jacket and insulation from RG-59 and RG-6 coaxial cable
- Durable blades cut copper-coated steel conductors
- Three crimping nests for crimping F-connectors and ring terminals



| Description                            | Cat. No. |
|--|----------|
| Coax Strip & Crimp Tool                | 30-433   |
| Coax Strip & Crimp Tool w/F-Connectors | 30-433F  |