

Pilot and Signaling Devices

Heavy-Duty 30.5 mm Watertight/Oiltight Accessories

CR104P

Accessories, Components and Kits
600 Volts max. AC/DC
10 Amperes Continuous

Mushroom-Head Guards

Mushroom-Head Cap Diameter	Depth (max. projection front of panel)	Product Number
1 3/8", OD = 1.66" (42.2 mm)	1.38" (35.1 mm)	CR104PXG14
2 3/8", OD = 2.64" (67.1 mm)	1.38" (35.1 mm)	CR104PXG15

Cluster-Type Pilot Light Boots

Color	Package Quantity	Product Number
Yellow	4	CR104PXL08E ¹
Green	4	CR104PXL08G ¹
Blue	4	CR104PXL08L ¹
Red	4	CR104PXL08R ¹
1 Each: Yellow, Green, Blue, Red	Four, 1 each color	CR104PXL08T

¹This price per each, packaged in quantities of 4. Must be ordered in multiples of 4.

Octagonal Operator Mounting Rings


For use with	Depth (max. projection front of panel)	Description	Product Number
Standard Flush Push Buttons, Push-to-test Pilot Lights, Mushroom-Head Push Buttons			CR104PXG01
Extended Push Buttons, Key-Operated Push Buttons, Push-to-latch/turn-to-release Push Buttons			CR104PXG02
Recessed Push Buttons	0.71" (19.0 mm)		CR104PXG03
Guarded Illuminated Push Buttons	1.20" (30.5 mm)		CR104PXG04
Combination (push/turn) Units			CR104PXG06
Non-illuminated Selector Switches, Joysticks, Potentiometer Operators			CR104PXG07
Standard Pilot Lights, Illuminated Selector Switches			CR104PXG08
Cluster Pilot Lights (2- and 4-lamp)			CR104PXG09
Octagonal Rings		CR104P octagonal ring wrench	CR104PXG104

Stainless Steel Flush Plate

Package Quantity	Product Number
1	CR2940BD201D



CR104PXG14 Mushroom-Head Guard



CR104PXL08* Cluster Light Boots



CR104PXG01 Octagonal Mounting Ring for Standard Flush and Mushroom-Head Push Buttons, and Push to Test Pilot Lights



CR104PXG04 Octagonal Mounting Ring for Guarded Illuminated Push Buttons



CR104PXG07 Octagonal Mounting Ring for Non-Illuminated Selector Switches, Joysticks and Potentiometer Operators



CR104PXG104 Octagonal Ring Wrench

