

Control Renewal Parts

Renewal Parts

For NEMA Rated 300- and 200-Line Magnetic Contactors and Starters
NEMA Sizes 00-7

Magnet Coil

NEMA Size	Starter Prefix	Product Number
00,0,1	300- and 200-Line	15D21G***
2	300- and 200-Line	15D22G***
3	300- and 200-Line	55-501336G***
4	300- and 200-Line	55-501463G***
5	200-Line	55-501493G***
5	300-Line	55-530249G***
6	300- and 200-Line	55-536548G*** ¹



Magnet Coil

***Coil Suffix Table

List prices are for coils with standard voltages and frequencies. For pricing of coils with special voltages and frequencies, refer to current issue of GEP-3910.

Voltage							
60 Hertz	24	115-120	200-208	230-240	265-277	460-480	575-600
Specify Suffix	024	002	023	003	013	004	005

Voltage					
50 Hertz	110	220	380	440	550
Specify Suffix	002	003	064	004	005


Note: The 002 coil suffix (115-120 V, 60 Hz/110V, 50 Hz) supersedes the 022 coil suffix (120 V, 60 Hz).

AC Replacement Coils

NEMA Size	Coil Voltage	Starter Prefix	Product Number
6	115/120	300- and 200-Line	55-522089G011 ²
6	200/208, 230	300- and 200-Line	55-522089G007 ²
6	380, 415	300- and 200-Line	55-522089G005 ²
6	460	300- and 200-Line	55-522089G004 ²
6	575	300- and 200-Line	55-522089G003 ²
7	115/120	300- and 200-Line	55-522003G009
7	200/208, 230	300- and 200-Line	55-522003G006
7	380, 415	300- and 200-Line	55-522003G004
7	460	300- and 200-Line	55-522003G003
7	575	300- and 200-Line	55-522003G002

Contact Kit

NEMA Size	No. of Poles	Starter Prefix	Product Number
00	4	300- and 200-Line	55-152313G009
0	4	300- and 200-Line	546A300G002
1	4	300- and 200-Line	546A301G053
2	3	300- and 200-Line	546A780G051
3	3	300- and 200-Line	55-153677G002
4	3	300- and 200-Line	55-153678G002
5	3	200-Line	55-154607G002
5	3	300-Line	55-154607G041
6	3	300- and 200-Line	55-186556G004 ¹
6	3	300- and 200-Line	232A6724G009 ²
6	2	300- and 200-Line	232A6724G011 ²
7	3	300- and 200-Line	232A6724G010
7	2	300- and 200-Line	232A6724G012



Contact Kit

200-Line Block Overload Relay

NEMA Size	Starter Prefix	Reference Number	Product Number
00, 0, 1	200-Line	CR224C310F	CR324C310F9X2 ³
2	200-Line	CR224D310F	CR324D310FX ³
3	200-Line	CR224E310F	CR324E310FX ³
4	200-Line	CR224F310F	CR324F310FX ³
5	200-Line	CR224G310F	CR324G310FX ^{3,4,5}



200-Line Block Overload Relay

¹Size 6 with 305HH, 306HH, 307HH, and 308HH nomenclature.

²Size 6 with 385H, 386H, 387H, 388H, and 389H nomenclature.

