

# Pilot and Signaling Devices

## Heavy-Duty 22.5 mm Watertight/Oiltight Accessories

### C-2000

#### Accessories

600 VAC Max., 300 VDC Max.

10 Amps Continuous AC, 2.5 Amps Continuous DC

#### Keys

Key Type	Key Number	Product Number
Standard	#3095	077C3095 <sup>1</sup>
Special	#3353	077C3353 <sup>1</sup>
Special	#9901	077C9901 <sup>1</sup>
Special	#9902	077C9902 <sup>1</sup>
Special	#9903	077C9903 <sup>1</sup>
Special	#9904	077C9904 <sup>1</sup>
Special	#9905	077C9905 <sup>1</sup>
Special	#9910	077C9910 <sup>1</sup>
Special	#9916	077C9916 <sup>1</sup>
Special	#9919	077C9919 <sup>1</sup>
Special	#R455 (Ronis key)	077CR455 <sup>1</sup>
Colored	#73033	077CF73033 <sup>1</sup>
Colored	#73034	077CF73034 <sup>1</sup>
Colored	#73037	077CF73037 <sup>1</sup>
Colored	#73038	077CF73038 <sup>1</sup>
Colored	#73040	077CF73040 <sup>1</sup>

<sup>1</sup>Package quantity is five; order in multiples of five.  
All include 2 Keys.

#### Lamps

Bulb Type	Voltage	Watts	Product Number
Incandescent	6 VAC/DC	0.6	BA9S606
Incandescent	6 VAC/DC	1.5	BA9S615
Incandescent	12 VAC/DC	2	BA9S122
Incandescent	24 VAC/DC	2	BA9S242
Incandescent	48 VAC/DC	2	BA9S48
Incandescent	60 VAC/DC	1.2	BA9S6012
Incandescent	130 VAC/DC	2	BA9S130
Neon	110 VAC <sup>2</sup>	0.077	BA9SN110
Neon	220 VAC <sup>3</sup>	0.33	BA9SN220
LED	6 VAC/DC	0.59	080BA9S6L*
LED	12 VAC/DC	0.78	080BA9S12L*
LED	24 VAC/DC	0.84	080BA9S24L*
LED	48 VAC/DC	1.12	080BA9S48L*
LED	120 VAC/DC	1.4	080BA9S120L*

<sup>2</sup>94 AC minimum starting voltage

<sup>3</sup>186 AC minimum starting voltage

Replace asterisk (\*) in LED Type product number from Colors table below.

#### \*LED Colors

Colors	Red	Green	Yellow	Orange	White	Blue
*Color Code	R	V	G	A	B	L



Keys



Enclosure Hole Plugs



Locking Ring Wrench



Ring Reducers, Black Plastic and Polished Chrome



Assembled 16-Device Tabletop Display



Lamps

