

#### Rear Mounting

Mounting Style	Handle Style	Number of Padlocks	Terminal Cover Included	IP	Handle/Lever Color	ML Switch Type	Ampere Rating	Product Number
Rear Panel or DIN Rail Mounting	Locking Lever	1 or 2	Yes	IP30	Red/Yellow	ML1	25A	D/640006-942
Rear Panel or DIN Rail Mounting	Locking Lever	1 or 2	Yes	IP30	Red/Yellow	ML1	40A	D/650006-942
Rear Panel or DIN Rail Mounting	Locking Lever	1 or 2	Yes	IP30	Red/Yellow	ML2	63A	D/660006-942
Rear Panel or DIN Rail Mounting	Locking Lever	1 or 2	Yes	IP30	Red/Yellow	ML2	80A	D/670006-942
Rear Panel or DIN Rail Mounting	Locking Lever	1 or 2	Yes	IP30	Red/Yellow	ML3	125A	D/680006-942
Rear Panel or DIN Rail Mounting	Locking Lever	1 or 2	Yes	IP30	Black/Gray	ML1	25A	D/640006-943
Rear Panel or DIN Rail Mounting	Locking Lever	1 or 2	Yes	IP30	Black/Gray	ML1	40A	D/650006-943
Rear Panel or DIN Rail Mounting	Locking Lever	1 or 2	Yes	IP30	Black/Gray	ML2	63A	D/660006-943
Rear Panel or DIN Rail Mounting	Locking Lever	1 or 2	Yes	IP30	Black/Gray	ML2	80A	D/670006-943
Rear Panel or DIN Rail Mounting	Locking Lever	1 or 2	Yes	IP30	Black/Gray	ML3	125A	D/680006-943
Rear Panel or DIN Rail Mounting	Standard Lever	-	No	IP30	Black	ML1	25A	D/640006-900
Rear Panel or DIN Rail Mounting	Standard Lever	-	No	IP30	Black	ML1	40A	D/650006-900
Rear Panel or DIN Rail Mounting	Standard Lever	-	No	IP30	Black	ML2	63A	D/660006-900
Rear Panel or DIN Rail Mounting	Standard Lever	-	No	IP30	Black	ML2	80A	D/670006-900
Rear Panel or DIN Rail Mounting	Standard Lever	-	No	IP30	Black	ML3	125A	D/680006-900
Door Coupling	Locking Lever	1 or 2	Yes	IP55	Red/Yellow	ML1	25A	D/640006-842
Door Coupling	Locking Lever	1 or 2	Yes	IP55	Red/Yellow	ML1	40A	D/650006-842
Door Coupling	Locking Lever	1 or 2	Yes	IP55	Black/Gray	ML1	25A	D/640006-843
Door Coupling	Locking Lever	1 or 2	Yes	IP55	Black/Gray	ML1	40A	D/650006-843
Door Coupling	Locking Rotary Handle	3	Yes	IP55	Red/Yellow	ML1	25A	D/640006-812
Door Coupling	Locking Rotary Handle	3	Yes	IP55	Red/Yellow	ML1	40A	D/650006-812
Door Coupling	Locking Rotary Handle	3	Yes	IP55	Red/Yellow	ML2	63A	D/660006-812
Door Coupling	Locking Rotary Handle	3	Yes	IP55	Red/Yellow	ML2	80A	D/670006-812
Door Coupling	Locking Rotary Handle	3	Yes	IP55	Red/Yellow	ML3	125A	D/680006-812
Door Coupling	Locking Rotary Handle	3	Yes	IP55	Black/Gray	ML1	25A	D/640006-813
Door Coupling	Locking Rotary Handle	3	Yes	IP55	Black/Gray	ML1	40A	D/650006-813
Door Coupling	Locking Rotary Handle	3	Yes	IP55	Black/Gray	ML2	63A	D/660006-813
Door Coupling	Locking Rotary Handle	3	Yes	IP55	Black/Gray	ML2	80A	D/670006-813
Door Coupling	Locking Rotary Handle	3	Yes	IP55	Black/Gray	ML3	125A	D/680006-813




Rear Panel or DIN-rail Mount, Locking Lever



Rear Panel or DIN-rail Mount, Standard Lever



Door Coupling, Locking Lever



Door Coupling, Locking Rotary Handle

See switching diagrams beginning on page 8-16. Diagram number corresponds to last three digits in base product number. For example, diagram number for D/640006-942 is 006.

