



Controller Accessories

Front Mounted (Internal) Accessories

Snap away the dust cover(s) and up to two front mounted accessories slide into the controller, increasing application flexibility without increasing width.

Image	Wiring Diagram	Accessory	Mounting Position	Contacts		Cat. No.	List Price, GO-10A2C
				1NO	1NC		
		Auxiliary Contact (B300/Q300)	Left or right front	1NO	GPAC10FBA	\$12.00	
				1NC	GPAC01FBA	12.00	
		Alarm Contact (B300/Q300)	Right front	1NO	GPAL10FRA	14.00	
				1NC	GPAL01FRA	14.00	
		Front Aux. Position Cover (Package of 10)	Left or right front	—	GPAC0VF1A	.50 each	

Side Mounted Accessories

Snap on accessories - maximum of [(2) auxiliary contact blocks] or [(1) auxiliary contact block plus (1) alarm/aux. block or (1) short circuit indicator] or [(1) alarm/auxiliary plus (1) short circuit indicator] left and (2) auxiliary contact blocks or (1) shunt trip or (1) undervoltage release right.

Image	Wiring Diagram	Accessory	Mounting Position	Contacts		Cat. No.	List Price, GO-10A2C
				2NO	1NO + 1NC		
		Auxiliary Contact (A600/P300)	Left	2NO	GPAC20LLA ^①	\$18.00	
				1NO + 1NC	GPAC11LLA ^①	18.00	
				2NC	GPAC02LLA ^①	18.00	
			Right	2NO	GPAC20LRA ^①	18.00	
				1NO + 1NC	GPAC11LRA ^①	18.00	
				2NC	GPAC02LRA ^①	18.00	
		Alarm/Auxiliary Contact (A600/P300)	Left	1NO Alarm + 1NO Aux.	GPAD1010LLA	24.00	
				1NO Alarm + 1NC Aux.	GPAD1001LLA	24.00	
				1NC Alarm + 1NO Aux.	GPAD0110LLA	24.00	
				1NC Alarm + 1NC Aux.	GPAD0101LLA	24.00	
		Short Circuit Alarm (A600/P300)	Left	1NO + 1NC	GPAE11LLA	15.00	
		Shunt Trip (de-energizes the controller when external operator interrupts circuit)	Right	Coil Voltage		Cat. No.	List Price, GO-10A2C
24V 60/50 Hz				GPASLRAA1	48.00		
48V 60 Hz				GPASLRAAF	48.00		
60V 60 Hz, 48V 50 Hz				GPASLRAAG	48.00		
120V 60 Hz, 110-127V 50 Hz				GPASLRAAJ	48.00		
208V 60 Hz				GPASLRAAM	48.00		
240V 60 Hz, 220V 50 Hz				GPASLRAAN	48.00		
277V 60 Hz, 240V 50 Hz				GPASLRAAR	48.00		
380/400V 50 Hz				GPASLRAAU	48.00		
460-480V 60 Hz, 415-440V 50 Hz				GPASLRAAW	48.00		
600V 60 Hz, 500V 50 Hz				GPASLRAAY	48.00		
24-60V DC				GPASLRADD	48.00		
110-240V DC	GPASLRADJ	48.00					

① GPS1BSAR and GPS1BHAR (24-32 FLA controllers) can accept all accessory combinations noted above except that only (1) lateral auxiliary contact block may be used on this size.