

## Voltage & Conduit Markers

- Identify junction boxes, switches, circuit breakers, raceways, pipe and fuse boxes
- Non-conductive for user safety
- High-adhesion properties with easy removability
- Vinyl-impregnated cloth construction for long-lasting durability
- Resist abrasion, moisture, dirt and oil
- Non-smear, black legend on bright orange background for high visibility



**Large:**  
2-1/4 in. x 9 in. each w/1-3/4 in. type



**Medium:**  
1-1/8 in. x 4-1/2 in. each w/3/4 in. type



**Small:**  
2-1/4 in. x 1/2 in. each w/5/16 in. type

Legend	Large Cat. No. 1/card	Medium Cat. No. 4/card	Small Cat. No. 18/card
120/208V	<b>44-295</b>	<b>44-296</b>	—
277/480V	<b>44-298</b>	<b>44-299</b>	—
120V	—	<b>44-353</b>	—
208V	—	<b>44-355</b>	—
240V	—	<b>44-358</b>	—
277V	—	—	<b>44-410</b>
480V	<b>44-314</b>	<b>44-364</b>	—
DANGER	<b>44-289</b>	—	—
HIGH VOLTAGE	<b>44-292</b>	—	—

### Specifications:

Temperature Range: -40°F to 180°F (-40°C to 82°C)  
Adhesion: 45 oz./in. width ultimate

## Heavy-Duty Lockout Tags

- High-visibility lettering
- Laminated plastic tags have non-fade legends, resist corrosive and harsh environmental conditions grommet
- Vinyl tags are silk screened with a 7/8 in. metal grommet; fastener included
- Exceeds OSHA's 50-lb. pullout requirement
- Matte finish for easy writing surface

Legend	Type	Qty.	Cat. No.
Do Not Operate	Heavy-Duty Laminated	5/card	<b>44-830</b>
	Heavy-Duty Laminated	100/box	<b>44-1830</b>
	Economy Vinyl	25/bag	<b>44-848</b>
Do Not Operate - Electricians at Work	Heavy-Duty Laminated	5/card	<b>44-832</b>
	Economy Vinyl	25/bag	<b>44-843</b>
Do Not Operate - (red striped background)	Heavy-Duty Laminated	5/card	<b>44-833</b>
	Heavy-Duty Laminated	100/box	<b>44-1833</b>
	Economy Vinyl	25/bag	<b>44-849</b>

## Lockout Signs

- Resistant to both chemicals and abrasion – protected graphics for indoor and outdoor use

Legend	Material	Size (In.)	Cat. No.
OSHA Regulation 36 in. clearance	Self-sticking polyester	3-1/2 x 10	<b>44-877</b>
OSHA Regulation (Bilingual) 36 in. clearance	Self-sticking polyester	7 x 10	<b>44-878</b>
Danger - Breakers Locked Out	Magnetic	5 x 7	<b>44-890</b>

## Safety Signs

- Resistant to both chemicals & abrasion – protected graphics for indoor & outdoor use



## Bilingual Lockout Tags

- Spanish/English tags provide extra safety and information in bilingual situations
- High-visibility lettering
- Laminated vinyl tags with non-fade legends resist corrosive and harsh environmental conditions
- Write-on tag with 7/8 in. grommet can be padlocked to device to help prevent unauthorized removal

Legend	Qty.	Cat. No.
Do Not Operate (striped)	5	<b>44-841</b>

Legend	Material	Size (In.)	Cat. No.
Danger – High Voltage	Fiberglass	10 x 14	<b>44-862</b>
Danger – High Voltage	Self-Sticking Polyester	7 x 10	<b>44-863</b>
Danger – High Voltage – Keep Out	Fiberglass	10 x 14	<b>44-880</b>
Danger – High Voltage – Keep Out	Self-Sticking Polyester	7 x 10	<b>44-881</b>
Danger – High Voltage – Spanish	Self-Sticking Polyester	7 x 10	<b>44-865</b>