


Molded Case Circuit Breakers

External Accessories

Door-Mounted Operators



TDM Operating Handle, Fixed or Adjustable Shaft

TDM Handle Operating Mechanisms, Door Mounted

Complete mechanism with handle UL listed, E-57253

Operating mechanism only, UL Component Recognized, E-57253

Breaker Type	Box Depth in Inches	Complete Mechanism ¹ with NEMA 1, 3R, 12 Handle Product Number	Operating Mechanism Only Product Number	Handle Only	
				NEMA 1, 3R, 12 Product Number	NEMA 4/4X Product Number
TQD, THQD	Extended Shaft 4 5/16 - 14 5/16	TQDHM2	TQDOM2 ²		
	Shallow Mount 4 3/16	TEFHM1	TEFOM1		
TEB, TEC, TB1, TED, THED	Extended Shaft 5-1/8 - 5 7/32 5 1/8 - 5 13/16 5 1/8 - 15	TEFHM3 TEFHM4 TEFHM2	TEFOM3 TEFOM4 TEFOM2	TH1	
TFC, TFJ, TFK, THFK	Shallow Mount 5 7/8 Extended Shaft 6 7/8 - 15 1/2	TFKHM1 TFKHM2	TFKOM1 TFKOM2 ²		THCH45 ^{3,4}
TJC, TJD, TJJ, TJK, THJK, TB4, TBC4	Shallow Mount 5 7/8 Extended Shaft 5 5/8 - 15 5/8	TJKHM1 TJKHM2	TJKOM1 TJKOM2 ⁴	TH2	
TKC, TKM, THKM, TB6, TBC6, TB8, TBC8	Shallow Mount 7 7/16 Extended Shaft 7 1/32 - 17 5/16	TKMHM1 TKMHM2	TKMOM1 TKMOM2 ⁴		
SE150 (GEH-5611) ⁵	4 3/16 6 1/8 - 15	SEFHM1 SEFHM2	SEFOM1 SEFOM2 ²	TH1	
SF250 (GEH-5611) ⁵	5 7/8 7 3/4 - 15 1/2	SEFHM1 SEFHM2	SEFOM1 SEFOM2 ²		THCH45 ^{3,4}
SG600 (GEH-5653) ⁵	5 7/8 5 5/8 - 15 5/8	SGHM1 SGHM2	SGOM1 SGOM2 ⁴	TH2	
SK1200 (GEH-5612) ⁵	6 7	SKHM1 SKHM2	SKOM1 SKOM2 ⁴		

¹Handle assembly and operating mechanism separately packaged.

²For 15-inch long shaft order Product Number 788A831G10. For 20-inch long shaft order Product Number 788A831G20.

³Provides interlocking for J600, SG600 SK1200, and K1200 breakers when used with the extended shaft operating mechanism. For interlocking with E150/SE150, F225 and SF250 order special shaft Product Number 788A832G1.

⁴For 15-inch long shaft order Product Number 788A832G2. For 20-inch long shaft order Product Number 788A832G5.

⁵Installation instructions publication number.

⁶MOD 1 is 7 7/16; MOD 2 is 8 3/32.

⁷MOD 1 is 7 3/16 - 17 3/16; MOD 2 is 7 15/16 - 17 15/16.

Handle Accessories for TDM Operating Mechanisms

Device	Product Number
Replacement neoprene gaskets for NEMA 1, 3R and 12 enclosures	
Use with TH1	788A742P3
Use with TH2	788A742P4

