

# WOOD BORING SELFEED BITS

## STANDARD SELFEED BITS

### FAST DRILLING

- Aggressive feed screw design allows the bit to pull through the wood faster

### CLEAN HOLES

- Alloy steel kerf cutters provide clean holes

### RESHARPENABLE

- Cutting edge can be resharpened



| Size    | Part Number | Qty | Shank Type | Entrance For Pipe and Rigid Conduit | Entrance For Tubing | Package Type |
|---------|-------------|-----|------------|-------------------------------------|---------------------|--------------|
| 1"      | 48-25-1001  | 1   | 7/16" Hex  | 1/2"                                | 7/8"                | Carton       |
| 1"      | 48-25-1002  | 1   | 7/16" Hex  | 1/2"                                | 7/8"                | Clamshell    |
| 1-1/8"  | 48-25-1121  | 1   | 7/16" Hex  | 1/2"                                | 1"                  | Carton       |
| 1-1/8"  | 48-25-1122  | 1   | 7/16" Hex  | 1/2"                                | 1"                  | Clamshell    |
| 1-1/4"  | 48-25-1251  | 1   | 7/16" Hex  | 3/4"                                | 1-1/8"              | Carton       |
| 1-1/4"  | 48-25-1252  | 1   | 7/16" Hex  | 3/4"                                | 1-1/8"              | Clamshell    |
| 1-3/8"  | 48-25-1371  | 1   | 7/16" Hex  | 1"                                  | 1-1/4"              | Carton       |
| 1-3/8"  | 48-25-1372  | 1   | 7/16" Hex  | 1"                                  | 1-1/4"              | Clamshell    |
| 1-1/2"  | 48-25-1501  | 1   | 7/16" Hex  |                                     | 1-3/8"              | Carton       |
| 1-1/2"  | 48-25-1502  | 1   | 7/16" Hex  |                                     | 1-3/8"              | Clamshell    |
| 1-3/4"  | 48-25-1751  | 1   | 7/16" Hex  | 1-1/4"                              | 1-1/2"              | Carton       |
| 1-3/4"  | 48-25-1752  | 1   | 7/16" Hex  | 1-1/4"                              | 1-1/2"              | Clamshell    |
| 2"      | 48-25-2001  | 1   | 7/16" Hex  | 1-1/2"                              | 1-7/8"              | Carton       |
| 2"      | 48-25-2002  | 1   | 7/16" Hex  | 1-1/2"                              | 1-7/8"              | Clamshell    |
| 2-1/8"  | 48-25-2121  | 1   | 7/16" Hex  |                                     | 2"                  | Carton       |
| 2-1/8"  | 48-25-2122  | 1   | 7/16" Hex  |                                     | 2"                  | Clamshell    |
| 2-1/4"  | 48-25-2251  | 1   | 7/16" Hex  |                                     | 2-1/8"              | Carton       |
| 2-1/4"  | 48-25-2252  | 1   | 7/16" Hex  |                                     | 2-1/8"              | Clamshell    |
| 2-9/16" | 48-25-2561  | 1   | 7/16" Hex  | 2"                                  | 2-1/2"              | Carton       |
| 2-9/16" | 48-25-2562  | 1   | 7/16" Hex  | 2"                                  | 2-1/2"              | Clamshell    |
| 3"      | 48-25-3001  | 1   | 3-Flat     | 2-1/2"                              | 2-7/8"              | Carton       |
| 3-5/8"  | 48-25-3621  | 1   | 3-Flat     | 3"                                  | 3-1/2"              | Carton       |
| 4-1/8"  | 48-25-4125  | 1   | 3-Flat     | 3**                                 |                     | Carton       |
| 4-5/8"  | 48-25-4621  | 1   | 3-Flat     | 4"                                  | 4-1/2"              | Carton       |

## STANDARD SELFEED BIT KITS

| 7 Pc Plumber's Kit<br>49-22-0065  | 7 Pc Contractor's Kit<br>49-22-0130   | 4 Pc Contractor's Kit<br>49-22-0135   |
|---|---|---|
| <b>Includes:</b> <ul style="list-style-type: none"> <li>(1) Each augers (7/8", 1-1/8", 1-1/4", 1-1/2")</li> <li>(1) Each selffeed bits (1-3/4", 2-1/8", 2-9/16")</li> <li>(1) 5-1/2" Hex key extension</li> </ul> | <b>Includes:</b> <ul style="list-style-type: none"> <li>(2) Each augers (7/8", 1-1/8", 1-1/4", 1-1/2")</li> <li>(1) Each selffeed bits (1", 1-1/8", 1-1/4", 1-1/2", 1-3/4", 2-1/8", 2-9/16")</li> <li>(1) 5-1/2" Hex key extension</li> </ul> | <b>Includes:</b> <ul style="list-style-type: none"> <li>(1) Each selffeed bits (1-3/8", 1-1/2", 2-1/8", 2-9/16")</li> <li>(1) 5-1/2" Hex key extension</li> </ul> |

## STANDARD SELFEED BIT ACCESSORIES

| Small Standard Selffeed Bit Accessory Kit<br>48-25-6000   | Coarse Thread Feed Screw for Selffeed Bit<br>48-28-6870  | 1/8" Hex Wrench for Selffeed Bit<br>49-96-0060   |
|---|--|--|
| <b>Includes set screws, feed screws and hex key for sizes:</b> <ul style="list-style-type: none"> <li>1" - 2-9/16"</li> </ul> | <b>Includes feed screw for sizes:</b> <ul style="list-style-type: none"> <li>1" - 2-9/16"</li> </ul> | <b>Includes hex wrench for sizes:</b> <ul style="list-style-type: none"> <li>1" - 2-9/16"</li> </ul> |
| Large Standard Selffeed Bit Accessory Kit<br>48-25-7000   | Replacement Feed Screw for Selffeed Bit<br>48-28-6880  | 5/32" Hex Wrench for Selffeed Bit<br>49-96-0070  |
| <b>Includes set screws, feed screws and hex key for sizes:</b> <ul style="list-style-type: none"> <li>3" - 4-5/8"</li> </ul>  | <b>Includes feed screw for sizes:</b> <ul style="list-style-type: none"> <li>3" - 4-5/8"</li> </ul>  | <b>Includes hex wrench for sizes:</b> <ul style="list-style-type: none"> <li>3" - 4-5/8"</li> </ul>  |

## EXTENSIONS

### UNIVERSAL FIT

- All extensions work with all major brands

### QUIK-LOK™ EXTENSIONS

- Fits any 1/4" or 7/16" hex shank product
- Impact rated for maximum durability
- Releases by hand for quick operation



HEX WRENCH



QUIK-LOK™

| Part Number | Shank Size | Length | Type       | Accepts Shank Size |
|-------------|------------|--------|------------|--------------------|
| 48-28-1000  | 1/4"       | 3"     | QUIK-LOK™  | 1/4"               |
| 48-28-1010  | 1/4"       | 6"     | QUIK-LOK™  | 1/4"               |
| 48-28-1020  | 1/4"       | 12"    | QUIK-LOK™  | 1/4"               |
| 48-28-4008  | 3/8"       | 12"    | Hex Wrench | 3/8"               |
| 48-28-1030  | 7/16"      | 5-1/2" | QUIK-LOK™  | 7/16"              |
| 48-28-1040  | 7/16"      | 12"    | QUIK-LOK™  | 7/16"              |
| 48-28-1050  | 7/16"      | 18"    | QUIK-LOK™  | 7/16"              |
| 48-28-1060  | 7/16"      | 24"    | QUIK-LOK™  | 7/16"              |
| 48-28-4001  | 7/16"      | 5-1/2" | Hex Wrench | 7/16"              |
| 48-28-4006  | 7/16"      | 12"    | Hex Wrench | 7/16"              |
| 48-28-4011  | 7/16"      | 18"    | Hex Wrench | 7/16"              |
| 48-28-4016  | 7/16"      | 24"    | Hex Wrench | 7/16"              |