

## STANDARD SELFEEED BITS

### FAST DRILLING

- Aggressive feed design allows the bit to pull through the wood faster

### CLEAN HOLES

- Alloy steel kerf cutters provide clean holes

### RESHARPENABLE

- Cutting edge can be resharpened



Size	Part Number	Qty	Shank Type	Entrance For Pipe and Rigid Conduit	Entrance For Tubing	Package Type
1"	48-25-1001	1	7/16" Hex	1/2"	7/8"	Carton
1"	48-25-1002	1	7/16" Hex	1/2"	7/8"	Clamshell
1-1/8"	48-25-1121	1	7/16" Hex	1/2"	1"	Carton
1-1/8"	48-25-1122	1	7/16" Hex	1/2"	1"	Clamshell
1-1/4"	48-25-1251	1	7/16" Hex	3/4"	1-1/8"	Carton
1-1/4"	48-25-1252	1	7/16" Hex	3/4"	1-1/8"	Clamshell
1-3/8"	48-25-1371	1	7/16" Hex	1"	1-1/4"	Carton
1-3/8"	48-25-1372	1	7/16" Hex	1"	1-1/4"	Clamshell
1-1/2"	48-25-1501	1	7/16" Hex		1-3/8"	Carton
1-1/2"	48-25-1502	1	7/16" Hex		1-3/8"	Clamshell
1-3/4"	48-25-1751	1	7/16" Hex	1-1/4"	1-1/2"	Carton
1-3/4"	48-25-1752	1	7/16" Hex	1-1/4"	1-1/2"	Clamshell
2"	48-25-2001	1	7/16" Hex	1-1/2"	1-7/8"	Carton
2"	48-25-2002	1	7/16" Hex	1-1/2"	1-7/8"	Clamshell
2-1/8"	48-25-2121	1	7/16" Hex		2"	Carton
2-1/8"	48-25-2122	1	7/16" Hex		2"	Clamshell
2-1/4"	48-25-2251	1	7/16" Hex		2-1/8"	Carton
2-1/4"	48-25-2252	1	7/16" Hex		2-1/8"	Clamshell
2-9/16"	48-25-2561	1	7/16" Hex	2"	2-1/2"	Carton
2-9/16"	48-25-2562	1	7/16" Hex	2"	2-1/2"	Clamshell
3"	48-25-3001	1	3-Flat	2-1/2"	2-7/8"	Carton
3-5/8"	48-25-3621	1	3-Flat	3"	3-1/2"	Carton
4-1/8"	48-25-4125	1	3-Flat	3**		Carton
4-5/8"	48-25-4621	1	3-Flat	4"	4-1/2"	Carton

## STANDARD SELFEEED BIT KITS

7 Pc Plumber's Kit 49-22-0065	7 Pc Contractor's Kit 49-22-0130	4 Pc Contractor's Kit 49-22-0135
<b>Includes:</b> <ul style="list-style-type: none"> <li>(1) Each augers (7/8", 1-1/8", 1-1/4", 1-1/2")</li> <li>(1) Each selffeed bits (1-3/4", 2-1/8", 2-9/16")</li> <li>(1) 5-1/2" Hex key extension</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>(2) Each augers (7/8", 1-1/8", 1-1/4", 1-1/2")</li> <li>(1) Each selffeed bits (1", 1-1/8", 1-1/4", 1-1/2", 1-3/4", 2-1/8", 2-9/16")</li> <li>(1) 5-1/2" Hex key extension</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>(1) Each selffeed bits (1-3/8", 1-1/2", 2-1/8", 2-9/16")</li> <li>(1) 5-1/2" Hex key extension</li> </ul>

## STANDARD SELFEEED BIT ACCESSORIES

Small Standard Selffeed Bit Accessory Kit 48-25-6000	Coarse Thread Feed Screw for Selffeed Bit 48-28-6870	1/8" Hex Wrench for Selffeed Bit 49-96-0060
<b>Includes set screws, feed screws and hex key for sizes:</b> <ul style="list-style-type: none"> <li>1" - 2-9/16"</li> </ul>	<b>Includes feed screw for sizes:</b> <ul style="list-style-type: none"> <li>1" - 2-9/16"</li> </ul>	<b>Includes hex wrench for sizes:</b> <ul style="list-style-type: none"> <li>1" - 2-9/16"</li> </ul>
Large Standard Selffeed Bit Accessory Kit 48-25-7000	Replacement Feed Screw for Selffeed Bit 48-28-6880	5/32" Hex Wrench for Selffeed Bit 49-96-0070
<b>Includes set screws, feed screws and hex key for sizes:</b> <ul style="list-style-type: none"> <li>3" - 4-5/8"</li> </ul>	<b>Includes feed screw for sizes:</b> <ul style="list-style-type: none"> <li>3" - 4-5/8"</li> </ul>	<b>Includes hex wrench for sizes:</b> <ul style="list-style-type: none"> <li>3" - 4-5/8"</li> </ul>

## EXTENSIONS

### UNIVERSAL FIT

- All extensions work with all major brands

### QUIK-LOK™ EXTENSIONS

- Fits any 1/4" or 7/16" hex shank product
- Impact rated for maximum durability
- Releases by hand for quick operation



HEX WRENCH



QUIK-LOK™

Part Number	Shank Size	Length	Type	Accepts Shank Size
48-28-1000	1/4"	3"	QUIK-LOK™	1/4"
48-28-1010	1/4"	6"	QUIK-LOK™	1/4"
48-28-1020	1/4"	12"	QUIK-LOK™	1/4"
48-28-4008	3/8"	12"	Hex Wrench	3/8"
48-28-1030	7/16"	5-1/2"	QUIK-LOK™	7/16"
48-28-1040	7/16"	12"	QUIK-LOK™	7/16"
48-28-1050	7/16"	18"	QUIK-LOK™	7/16"
48-28-1060	7/16"	24"	QUIK-LOK™	7/16"
48-28-4001	7/16"	5-1/2"	Hex Wrench	7/16"
48-28-4006	7/16"	12"	Hex Wrench	7/16"
48-28-4011	7/16"	18"	Hex Wrench	7/16"
48-28-4016	7/16"	24"	Hex Wrench	7/16"