

Accessories

Coils

To complete coil catalog number, replace the circled number with the appropriate "Frequency/Voltage Designation Letter/Digit" (from the **CL Frequency/Voltage Selection** table) corresponding to the voltage and frequency of the control circuit.



For CL Contactors, Alternating Current (AC)

For Use With	Catalog No.	Weight
5-15 hp contactors (CL00A, CL01A, CL02A, CL25A)	LB1A ^①	2.2 oz.
20-25 hp contactors (CL04A, CL45A)	LB3A ^①	3.7 oz.
30-75 hp contactors (CL06A, CL07A, CL08A, CL09A, CL10A)	LB4A ^①	5.2 oz.

For CL Contactors, Direct Current (DC)

For Use With	Catalog No.	Weight
5-15 hp contactors (CL00D, CL01D, CL02D, CL25D)	LB1D ^②	6 oz.
20-25 hp contactors (CL04D, CL45D)	LB3D ^②	9 oz.

CL Frequency/Voltage Selection

Please Note: Frequency/voltage combinations in bold are available by special order only.

① AC Voltage			② DC Voltage	Frequency/Voltage Designation Letter/Digit	① AC Voltage			② DC Voltage	Frequency/Voltage Designation Letter/Digit
60 Hz	50 Hz	50/60 Hz			60 Hz	50 Hz	50/60 Hz		
			12	B				250	T
24				C	380				V
	24		24	D	480	380/400			U
	32		36	E		415			W
48	42		42	F		440			X
	48		48	G					Y
110			60	H	600	500			Z
			72	I		660/690			
120	110		110	J			24		1
	127		120/125	K			42		2
208				L			110/115		3
220				M			120		4
277	220/230		220	N			220		5
	240			R			230		6
240				S			240		7
							440		8

Special order coils (Bold):

Minimum order, LB1A*: 20 units
Minimum order, all others: 10 units

For CK Contactors, 50/60 Hz AC or DC Electronic Coils

For Use With	Item	Catalog Number	Weight
3-pole 100-125 hp CK75C, CK08C	Coils for use with electronic coil	KB4E ^③	4lb. 2 oz.
	Electronic module	KM4E ^③	7 oz.
3-pole 150-250 hp CK08B, CK09B CK95B	Coils for use with electronic coil	KB5E ^③	4lb. 2 oz.
	Electronic module	KM5E ^③	7 oz.
3-pole 500 hp CK10B, CK11B CK12B 4-pole 125-250 hp CK08B, CK09B CK95B	Coils for use with electronic coil	KB6E ^③	4lb. 2 oz.
	Electronic module	KM6E ^③	7 oz.
3-pole 300-400 hp CK10C, CK11C	Coils for use with electronic coil	KB7E ^③	4lb. 2 oz.
4-pole 300-400 hp CK10C, CK11C	Electronic module	KM7E ^③	7 oz.

For CL Contactors, 50/60 Hz AC or DC Electronic Coils

For Use With	Item	Catalog Number	Weight
3-pole 30-75 hp CL06E, CL07E, CL08E, CL09E, CL10E	Electronic coil and module combination	LM4E ^④	4lb. 2 oz.

Electronic Coil Voltage Selection for CL and CK Contactors

Voltage	Voltage Designation Letter ^⑤
24-28	D
42-48	F
110-127	J
220-250	N
380-415	U
440-500	Y