




18 TPI Sub-Compact Portable Band Saw Blade (3 PK)

48-39-0572

What's Included

(1) 18 TPI Sub-Compact Portable Band Saw Blade (3 PK) (48-39-0572)



Features

- Matrix II high speed steel teeth deliver maximum durability
- Alloy backing steel provides extended blade life
- Precision formed teeth create fast, clean cuts
- For cutting common materials 5/32" - 3/16" thick and very hard materials 3/16" - 5/16" thick

Specifications

TPI	18
Pack Qty	3
Blade Dimensions	27" X 1/2" X .020"

Overview

Milwaukee Sub-Compact Portable Band Saw Blades are designed to maximize performance of the Milwaukee M12 Cordless Sub-Compact Band Saw. They will deliver long tooth life and exceptional durability in metal-cutting applications, including strut, conduit, angle iron, copper tube, threaded rod, and pipe. Tooth form, pitch, and set have been designed to deliver straight, accurate cuts across a broad range of materials.

Available April 2012

Model Options

Item/Cat #	TPI	Blade Dimensions	Pack Qty	
48-39-0507	10	35-3/8" x 1/2" x .020"	100 (Bulk)	FIND RETAILERS
48-39-0508	10	35-3/8" x 1/2" x .020"	1	FIND RETAILERS
48-39-0509	10	35-3/8" x 1/2" x .020"	3	FIND RETAILERS
48-39-0517	14	35-3/8" x 1/2" x .020"	100 (Bulk)	FIND RETAILERS
48-39-0518	14	35-3/8" x 1/2" x .020"	1	FIND RETAILERS
48-39-0519	14	35-3/8" x 1/2" x .020"	3	FIND RETAILERS

Item/Cat #	TPI	Blade Dimensions	Pack Qty	
48-39-0527	18	35-3/8" x 1/2" x .020"	100 (Bulk)	FIND RETAILERS
48-39-0528	18	35-3/8" x 1/2" x .020"	1	FIND RETAILERS
48-39-0529	18	35-3/8" x 1/2" x .020"	3	FIND RETAILERS
48-39-0537	24	35-3/8" x 1/2" x .020"	100 (Bulk)	FIND RETAILERS
48-39-0538	24	35-3/8" x 1/2" x .020"	1	FIND RETAILERS
48-39-0539	24	35-3/8" x 1/2" x .020"	3	FIND RETAILERS
48-39-0572	18	27" X 1/2" X .020"	3	FIND RETAILERS

[View Mobile Site](#)

© 2014 by Milwaukee Electric Tool Corporation. All rights reserved. ||| MS2