



SAWZALL® BLADES

WOOD CUTTING SAWZALL® BLADES



The Ax™ wood-cutting blades are designed to provide tough, straight cuts in nail-embedded wood and engineered lumber. Choose The Ax™ blades for straighter door and window cut-outs or for greater tooth durability when cutting a lot of nails. The Ax™ blades are 1" tall and .060" thick.

Thin Kerf wood-cutting blades are designed to provide fast, flexible cuts in nail-embedded wood and engineered lumber. Choose Thin Kerf blades for flush cuts and scroll cuts or for slightly faster cutting in dimensional lumber, plywood and OSB. Thin Kerf wood-cutting blades are 3/4" tall and .050" thick.

THE AX™ TOUGH STRAIGHT CUTS

TPI	Length	Materials	5 Packs	25 Packs	Bulk (25)	Bulk (100)
5	6"		48-00-5021	48-00-8021	48-01-2021	48-01-7021
5	9"		48-00-5026	48-00-8026	48-01-2026	48-01-7026
5	12"		48-00-5027	48-00-8027	48-01-2027	48-01-7027

THIN KERF FAST FLEXIBLE CUTS

5 Packs	25 Packs	50 Packs	Bulk (25)	Bulk (100)
48-00-5035	—	48-01-6035	48-01-2035	48-01-7035
48-00-5036	48-00-8036	48-01-6036	48-01-2036	48-01-7036
48-00-5037	—	48-01-6037	48-01-2037	48-01-7037

ROUGH-IN
48-00-1610

IDEAL FOR TIGHT RADIUS CUTS

FLUSH CUT
48-00-1600

IDEAL FOR DOOR CUT-OUTS

GENERAL PURPOSE SAWZALL® BLADES

Both Thin Kerf and The Wrecker™ general purpose blades are designed to handle the broadest spectrum of applications. Choose general purpose blades when cutting wood, plastic and metal at the same time or when you need to quickly switch between applications without changing your blade.

WRECKER™

TACKLE ANYTHING



The Wrecker™ general purpose blades are designed for true demolition work. Choose The Wrecker™ blades when you need tough cuts in nail-embedded wood, plaster and ferrous and non-ferrous metals. The Wrecker™ blades are 1" tall and .060" thick.

Thin Kerf general purpose blades are designed to provide fast, flexible cuts in woods, plastics and metals. Thin Kerf general purpose blades are 3/4" tall and .050" thick.

THE WRECKER™ TOUGH STRAIGHT CUTS

TPI	Length	Materials	5 Packs	25 Packs	Bulk (25)	Bulk (100)
8	6"		48-00-5701	48-00-8701	48-01-2701	48-01-7701
8	9"		48-00-5706	48-00-8706	48-01-2706	48-01-7706
8	12"		48-00-5711	48-00-8711	48-01-2711	48-01-7711
8/12	6"		—	—	—	—
8/12	8"		—	—	—	—
8/12	12"		—	—	—	—

THIN KERF FAST FLEXIBLE CUTS

5 Packs	25 Packs	50 Packs	Bulk (25)	Bulk (100)
—	—	—	—	—
—	—	—	—	—
—	—	—	—	—
48-00-5091	—	48-01-6091	—	48-01-7091
48-00-5093	48-00-8093	48-01-6093	48-01-2093	48-01-7093
48-00-5094	—	48-01-6094	48-01-2094	—



The same Ice Hardened™ cryogenic treatment that is available in metal cutting blades is also available in general purpose blades.

THE WRECKER™ TOUGH STRAIGHT CUTS

TPI	Length	Materials	5 Packs	25 Packs	Bulk (25)	Bulk (100)
8/12	6"		—	—	—	—
8/12	8"		—	—	—	—

THIN KERF FAST FLEXIBLE CUTS

5 Packs	25 Packs	50 Packs	Bulk (25)	Bulk (100)
48-00-4091	—	48-01-8091	—	48-01-9091
48-00-4093	—	48-01-8093	—	48-01-9093