



## **SDS-PLUS MASONRY BITS**

### **SDS+ ROTARY HAMMER BITS**

#### **4-CUTTER PREMIUM MX4 SDS+ CARBIDE BITS**

#### **LONG LIFE**

■ 4-Cutter solid carbide tip for up to 3X life in rebar



#### **ACCURATE HOLES**

■ Centering tip and 4-Cutter design drills more accurate holes for anchoring applications

	crioring app	0.1000.0110			
Size	Useable Length	Overall Length	Individual Part Number	Bulk Part Number	Bulk Qty
3/16"	2"	4"	48-20-7310	-	-
3/16"	4"	6"	48-20-7311	48-20-7911	15
3/16"	6"	8"	48-20-7312	-	-
3/16"	8"	10"	48-20-7313	-	-
3/16"	10"	12"	48-20-7314	-	-
1/4"	2"	4"	48-20-7330	-	-
1/4"	4"	6"	48-20-7331	48-20-7931	15
1/4"	6"	8"	48-20-7332	-	-
1/4"	8"	10"	48-20-7334	-	-
1/4"	10"	12"	48-20-7335	-	-
5/16"	4"	6"	48-20-7341	-	-
3/8"	4"	6"	48-20-7351	48-20-7951	10
3/8"	10"	12"	48-20-7354	-	-
3/8"	16"	18"	48-20-7357	-	-
1/2"	4"	6"	48-20-7371	48-20-7971	10
1/2"	10"	12"	48-20-7374	-	-
1/2"	16"	18"	48-20-7377	-	-



#### **4-CUTTER SDS+ BITS**

#### DURABLE

■ 4-Cutter design lasts longer when encountering small diameter rebar and mesh

#### **ACCURATE STARTS**

■ Centering point ensures correct hole placement

#### **FASTER** DRILLING

■ Unique face design directs dust through the 4 fluted spiral for faster drilling

Size	Part Number	Useable Length	Overall Length
5/8"	48-20-7200	6"	8"
5/8"	48-20-7203	10"	12"
5/8"	48-20-7206	16"	18"
3/4"	48-20-7210	6"	8"
3/4"	48-20-7215	10"	12"
3/4"	48-20-7220	16"	18"
7/8"	48-20-7225	6"	8"
7/8"	48-20-7230	10"	12"
7/8"	48-20-7236	16"	18"
1"	48-20-7240	8"	10"
1"	48-20-7246	16"	18"
1-1/8"	48-20-7250	8"	10"
1-1/8"	48-20-7256	16"	18"

# **INDUSTRY'S ONLY DUST EXTRACTOR**

Compatible with major power tool brands of SDS Plus Rotary Hammers and AC/DC Hammer Drills, the M12<sup>™</sup> HAMMERVAC<sup>™</sup> Universal Dust Extractor is the industry's only UNIVERSAL dust extractor.







**99.97% EFFICIENT** AT REMOVING PARTICLES 0.3µM FILTER AND ABOVE



## M12

## **HAMMERVAC™** Universal Dust Extractor Kit (2306-22)

**Universal Handle System:** 

Compatible with major brands of SDS Plus Rotary Hammers and AC & DC Hammer Drills

Replaceable Certified HEPA Filter: High quality debris filtration and lowest cost of ownership

Self-Powered by M12™ REDLITHIUM™ **Batteries:** 

No cords or hoses for maximum portability

3-Mode Switch with Auto-On: Auto-on mode turns HAMMERVAC™ on and off automatically

**Powerful Suction for Dust Extraction:** Reduces the potential for silica dust inhalation by user