



C-2000™ Mini-Contactors Accessories



Mechanical Interlock

Used for field assembly of reversing contactors and starters. Kit contains operating lever and 2 keys for joining either ac or dc contactors.

**Packaged in multiples of 10 units.
Each catalog number represents one unit.**

Catalog Number	List Price, GO-10A1	Approximate Weight Each
MMH0	\$8.00	0.1 oz.

Electronic Timer



Attaches either to the top or side of contactor or relay. Wired in series with the coil. May be used either with ac or dc coils. Timer operation range .5-60 seconds.

**Packaged in multiples of 10 units.
Each catalog number represents one unit.**

Coil Voltage AC, DC	Catalog Number	List Price, GO-10A1	Approximate Weight Each
24-240 V	MREBC10AC2	\$75.00	2 oz.


Electronic Timer Base

Allows timer to be either DIN rail- or panel-mounted.

**Packaged in multiples of 10 units.
Each catalog number represents one unit.**

Catalog Number	List Price, GO-10A1	Approximate Weight Each
MVB0R	\$10.00	0.2 oz.

Surge Suppressor



Used to protect control circuits from voltage transients. Plugs into front of contactor, no external wiring required. RC type for ac and diode for dc.

**Packaged in multiples of 10 units.
Each catalog number represents one unit.**


Coil Voltage Range	Catalog Number	List Price, GO-10A1	Approximate Weight Each
12-60V 50/60 Hz	MP0AAE1	\$16.00	0.5 oz.
72-240V 50/60 Hz	MP0AAE2	16.00	0.5 oz.
6-240 Vdc	MP0CAE3	16.00	0.5 oz.

Power Conductors for Reversing Contactor

Used to parallel the input terminals and reverse output terminals of reversing contactors. Consists of six solid-formed wires.

**Packaged in multiples of 10 units.
Each catalog number represents one unit.**

Catalog Number	List Price, GO-10A1	Approximate Weight Each
MVM01	\$16.00	0.5 oz.



References:

- Instructions
- GEH-5475 MC Mini-Contactor/MT0 Thermal-Overload relay. U.S. version.
- GEH-5931 MC Mini-Contactor Global Instructions
- GEH-5932 MT0 Thermal-Overload Relay Global Instructions

AC Replacement Coils for Contactors and Control Relays

Coil Voltage		Catalog Number	List Price, GO-10A1	Approximate Weight Each
60 Hz	50 Hz			
6		MBOAAⓄ	\$14.00	2 oz.
12		MBOABⓄ	14.00	2 oz.
24		MBOACⓄ	14.00	2 oz.
	24	MBOADⓄ	14.00	2 oz.
32		MBOAEⓄ	14.00	2 oz.
48	42	MBOAFⓄ	14.00	2 oz.
60	48	MBOAGⓄ	14.00	2 oz.
110		MBOAHⓄ	14.00	2 oz.
120	110	MBOAJⓄ	14.00	2 oz.
	115-127	MBOAKⓄ	14.00	2 oz.
208-220		MBOAMⓄ	14.00	2 oz.
240	220-230	MBOANⓄ	14.00	2 oz.
277	230-240	MBOARⓄ	14.00	2 oz.
	260	MBOASⓄ	14.00	2 oz.
380		MBOATⓄ	14.00	2 oz.
440	380-400	MBOAUⓄ	14.00	2 oz.
480	415-440	MBOAWⓄ	14.00	2 oz.
600	500	MBOAYⓄ	14.00	2 oz.
12	12	MBOA10Ⓞ	14.00	2 oz.
24	24	MBOA1Ⓞ	14.00	2 oz.
42	42	MBOA2Ⓞ	14.00	2 oz.
110-115	110-115	MBOA3Ⓞ	14.00	2 oz.
120	120	MBOA4Ⓞ	14.00	2 oz.
220	220	MBOA5Ⓞ	14.00	2 oz.
230	230	MBOA6Ⓞ	14.00	2 oz.
240	240	MBOA7Ⓞ	14.00	2 oz.
440	440	MBOA8Ⓞ	14.00	2 oz.

Ⓞ Sold in multiples of 10 only.

DC Replacement Coils for Contactors and Control Relays

Coil Voltage DC	Coil Wattage	Catalog Number	List Price, GO-10A1	Approximate Weight Each
6	3	MBOCAⓄ	\$18.00	3 oz.
12	3	MBOCB	18.00	3 oz.
24	3	MBOCD	18.00	3 oz.
32	3	MBOCCⓄ	18.00	3 oz.
36	3	MBOCEⓄ	18.00	3 oz.
42	3	MBOCFⓄ	18.00	3 oz.
48	3	MBOCG	18.00	3 oz.
60	3	MBOCHⓄ	18.00	3 oz.
72	3	MBOCIⓄ	18.00	3 oz.
110	3	MBOCJⓄ	18.00	3 oz.
120	3	MBOCKⓄ	18.00	3 oz.
125	3	MBOCL	18.00	3 oz.
220	3	MBOCNⓄ	18.00	3 oz.
240	3	MBOCRⓄ	18.00	3 oz.
250	3	MBOCS	18.00	3 oz.
15	1.2	MBOI9Ⓞ	18.00	3 oz.
24	1.2	MBOIDⓄ	18.00	3 oz.
24	2	MBOKDⓄ	18.00	3 oz.

Ⓞ Sold in multiples of 10 only.

**Technical Information... pages 3-66 to 3-70
Dimensions and
Weights..... pages 3-71 to 3-76**

3 IEC DEVICES