

TAPE MEASURES

UP TO **10X** LONGER LIFE



| General Information | | Tool Specifications | | | Application Specifications | |
|---------------------|--------------------------------|---------------------|----------|---------------------------------|----------------------------|-----------------------------------|
| Part # | Description | Graduation Type | Magnetic | Tape Color | Hook Type | Blueprint Scale |
| 48-22-5116 | 16' Magnetic Tape Measure | Inches | YES | Yellow (top) and White (bottom) | 360° | 1/4": 1', 1/8": 1' |
| 48-22-5117 | 16' Tape Measure* | Inches | | Yellow (top) and White (bottom) | 360° | 1/4": 1', 1/8": 1' |
| 48-22-5125 | 25' Magnetic Tape Measure | Inches | YES | Yellow (top) and White (bottom) | 360° | 1/4": 1', 1/8": 1' |
| 48-22-5126 | 25' Tape Measure* | Inches | | Yellow (top) and White (bottom) | 360° | 1/4": 1', 1/8": 1' |
| 48-22-5130 | 30' Magnetic Tape Measure* | Inches | YES | Yellow (top) and White (bottom) | 360° | 1/4": 1', 1/8": 1' |
| 48-22-5131 | 30' Tape Measure* | Inches | | Yellow (top) and White (bottom) | 360° | 1/4": 1', 1/8": 1' |
| 48-22-5135 | 35' Magnetic Tape Measure* | Inches | YES | Yellow (top) and White (bottom) | 360° | 1/4": 1', 1/8": 1' |
| 48-22-5136 | 35' Tape Measure* | Inches | | Yellow (top) and White (bottom) | 360° | 1/4": 1', 1/8": 1' |
| 48-22-5216 | 5m/16' Magnetic Tape Measure | Inches/Centimeters | YES | Yellow (top) and White (bottom) | 360° | 1/4": 1', 1/8": 1' and 1:50, 1:20 |
| 48-22-5217 | 5m/16' Tape Measure* | Inches/Centimeters | | Yellow (top) and White (bottom) | 360° | 1/4": 1', 1/8": 1' and 1:50, 1:20 |
| 48-22-5225 | 8m/26' Magnetic Tape Measure | Inches/Centimeters | YES | Yellow (top) and White (bottom) | 360° | 1/4": 1', 1/8": 1' and 1:50, 1:20 |
| 48-22-5226 | 8m/26' Tape Measure* | Inches/Centimeters | | Yellow (top) and White (bottom) | 360° | 1/4": 1', 1/8": 1' and 1:50, 1:20 |
| 48-22-5233 | 10m/33' Magnetic Tape Measure* | Inches/Centimeters | YES | Yellow (top) and White (bottom) | 360° | 1/4": 1', 1/8": 1' and 1:50, 1:20 |
| 48-22-5234 | 10m/33' Tape Measure* | Inches/Centimeters | | Yellow (top) and White (bottom) | 360° | 1/4": 1', 1/8": 1' and 1:50, 1:20 |
| 48-22-5305 | 5m Magnetic Tape Measure* | Centimeters | YES | Yellow (top) and White (bottom) | 360° | 1:50, 1:20 |
| 48-22-5306 | 5m Tape Measure* | Centimeters | | Yellow (top) and White (bottom) | 360° | 1:50, 1:20 |
| 48-22-5308 | 8m Magnetic Tape Measure* | Centimeters | YES | Yellow (top) and White (bottom) | 360° | 1:50, 1:20 |
| 48-22-5309 | 8m Tape Measure* | Centimeters | | Yellow (top) and White (bottom) | 360° | 1:50, 1:20 |

*Coming Soon