



Search MilwaukeeTool.com

NEW PRODUCTS & OFFERS

▼ TOOLS

▼ ACCESSORIES

▼ TEST & MEASUREMENT

▼ PARTS & SERVICE

▼ NEWS & MEDIA

BUY NOW

Home > Products > Tools > Cordless Tools > Combo Kits > M18™ Cordless 4-Tool Combo Kit

SHARE

PRINT

M18™ Cordless 4-Tool Combo Kit 2691-24

Buy Local



Related Items





Circular Saw Blade 6-1/2 in. 40 Carbide Teeth (1 per pack)



20 Piece Thunderbolt® Black and Bronze Drill Bit Set



M18™ XC High Capacity LITHIUM-ION Battery

[+ More Related Items](#)


Photos

Videos

The Milwaukee Advantage

The 2691-24 M18™ cordless 4-tool combo kit includes the Compact Driver (2601-20), Sawzall® Recip Saw (2620-20), Circular Saw (2630-20), and Work Light (49-24-0171). The M18™ Cordless System's patented technologies and electronics, innovative motor design, and superior ergonomics provide the most efficient blend of power, weight and performance in the industry. Powered by LITHIUM-ION, the M18™ cordless system delivers more torque, more power, and longer run-time than the competition.

Features

M18™ ½" Compact Drill/Driver Delivers 400 in-lbs of Torque and is Only 7 ¾" Long

M18™ Sawzall® Reciprocating Saw with Patented Gear-Protecting Clutch and Counter Balance Mechanism

M18™ 6 ½" Circular Saw Delivers 3,500 RPM with Magnesium Upper and Lower Guards for Maximum Durability

M18™ Work Light Provides a Fold-Away Hook for Hands Free Use and a 135-Degree Rotating Head to Direct Light at the Work Area

Specifications

Voltage	18V
Battery	(2) 18V XC High Capacity LITHIUM-ION Batteries
Charger	1-Hour Charger
Number of Tools	4
Carrier	Contractor Bag
Shipping Weight	29 lbs.

Includes

- Compact Driver (2601-20)
- Sawzall® Recip Saw (2620-20)
- Circular Saw (2630-20)
- Work Light (49-24-0171)
- (2) 18V LITHIUM-ION XC Battery Pack (48-11-1828)
- 18V Charger (48-59-1801)
- Side Handle
- (1) General Purpose Sawzall® Blade
- (1) Circ. Saw Blade
- Contractor Bag.

Sign Up for the Heavy Duty Club



Products

[New Products & Offers](#)
[Tools](#)
[Accessories](#)
[Test & Measurement](#)
[Milwaukee Gear](#)
[Catalog Request](#)

Parts & Service

[Test & Measure Service](#)
[Find a Service Center](#)
[Download Manuals](#)
[Parts Pricing](#)
[Milwaukee Warranty](#)
[Lightning Max Repair](#)
[FAQ's](#)

News & Media

[Press Releases](#)
[Product Reviews](#)
[Media Center](#)
[Media Inquiries](#)

About Us

[Milwaukee Story](#)
[Careers](#)
[Locations](#)
[Buy Now](#)
[Contact Us](#)