

## Assorted die kits

—  
01 Side A  
—  
02 Side B



—  
01



—  
02

### EZ-CK SS DIEKIT — Die sets kit

All the ABB dies you need to crimp the complete ABB EZGround® connector offering, presented in a two-sided metal carrying case. The reverse side of this kit allows you to keep all your colour-coded Color-Keyed crimping dies in one convenient location. A cable vs die reference chart inside each cover lets you sort and organize all your Color-Keyed compression connector dies for either copper or aluminum conductors. Additional compartments for cutting dies and adaptors round off this great package.



Cat no.	Die cat. no.	Qty.	Die colour	Copper (AWG or kcmil)	Aluminum (AWG or kcmil)
<b>Die sets kit</b>					
EZ-CK SS DIEKIT	15528SS	—	Brown	2	—
	15513SS	—	Green	1	4 AWG
	15508SS	—	Pink	1/0	2 AWG
	15526SS	—	Black	2/0	1 (Gold)
	15530SS	—	Orange	3/0	1/0 (Tan)
	15511SS	—	Purple	4/0	2/0 (Olive)
	15510SS	—	Yellow	250	—
	15534SS	—	White	300	4/0
	15514SS	—	Red	350	250
	15506SS	—	Brown	500	350
	15515SS	—	Black	750	650
	15G121R	—	—	—	—
	15G86R	—	—	—	—
	15501A	—	—	—	—
	15G126R	—	—	—	—
	CTB8	—	—	—	—
	COLCHA2-E	—	—	—	—
	GRNDIESEL-E	—	—	—	—

Assorted die kits



OD-TOOL-KIT

This kit is offered in a metal carrying case with heavy-duty handle and sturdy closures. The best way to carry the connectors and tools you need for commercial and residential hook-ups.

Cat no.	Kit includes	Qty.
OD-TOOL-KIT	Metallic carrying case	1
	ODB1 – Blackburn® Compression Tool	1
	WR159 – Compression connectors	18
	WR189 – Compression connectors	12
	WR289 – Compression connectors	5
	WR379 – Compression connectors	5
	WR419 – Compression connectors	5
	C5C – Insulating covers	30
	C7C – Insulating covers	15

ODB compression tool with straight wooden handles and ODH1 insulated heat cover (installed on ODB1) can be ordered separately.



TBM45SKIT-N

TBM45SKIT-N includes the following:

Cat no.	Qty.	Cat. no.	Cable size (AWG)	Items	Weight/lb each
TBM45SKIT-N	25	54130	#8	One-hole lugs	20
	25	54105	#6	One-hole lugs	20
	25	54106	#4	One-hole lugs	20
	25	54107	#2-#3	One-hole lugs	20
	25	54108	#1	One-hole lugs	20
	25	54143-TB	#2	One-hole lugs	20
	25	54136	#6	One-hole lugs	20
	25	54804	#8	2-way connectors	20
	25	54805	#6	2-way connectors	20
	25	54806	#4	2-way connectors	20
	25	54807	#2-#3	2-way connectors	20
	25	54808	#1	2-way connectors	20
	1	TBM45S Tool	-	-	20

## Assorted die kits



Cat no.	Description
PWK1	Empty case – includes Color-Keyed wall chart; make up your own selection of Color-Keyed lugs, splices, taps or motor disconnects
PWK4	Metal cabinet that holds four of the PWK1 shells slide out for easy removal of PWK1
MDPWK12	Selection of size 1 and 2 male motor disconnects plus insulators; to connect 60 single line to single line load motor leads, #12 AWG through #2 AWG; tools not included
MDPWK23	Selection of size 2 and 3 male motor disconnects plus insulators; to connect 54 single line to single line load motor leads, #12 AWG through 4/0 AWG; tools not included
MDKITL	Includes tool

### Carrying cases

Case contents MDPWK12				
1 PWK1	10 MD1210F-1	6 MD8M-2	6 MD8F-2	30 BOOT-1
10 MD1210M-1	10 MD8F-1	6 MD6M-2	6 MD6F-2	6 MD1210M-2
10 MD8M-1	10 MD6F-1	6 MD4M-2	6 MD4F-2	6 MD1210F-2
10 MD6M-1	30 MDBOOT-2	6 MD2M-2	6 MD2F-2	–
Case contents MDPWK23				
1 PWK1	6 MD1210F-2	3 MD2M-3	3 MD2F-3	6 MD1M-2
6 MD1210M-2	6 MD8F-2	3 MD1M-3	3 MD1F-3	36 MDBOOT-2
6 MD8M-1	6 MD6F-2	3 MD10M-3	3 MD10F-3	18 MDBOOT-3
6 MD6M-1	6 MD4F-2	3 MD20M-3	3 MD20F-3	–
6 MD4M-1	6 MD2F-2	3 MD30M-3	3 MD30F-3	–
6 MD2M-1	6 MD1F-2	3 MD40M-3	3 MD40F-3	–
Case contents MDKITL				
1 PWK1	1 TBM45S	24 MDBOOT-2	3 M2D2M-2	6 MD8M-1
3 M2D4M-2	3 M2D6M-2	3 M2D8M-2	12 M2DBOOT-2	6 MD8F-1
12 MDBOOT-1	12 MD2F-2	12 MD4F-2	12 MD6F-2	6 MD8M-2
12 M2D8M-2	6 MD2M-2	6 MD4M-2	6 MD6M-2	6 MD6M-2
6 MD6F-1	–	–	–	–