

STANDARD APPLIANCE ROCKERS



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6




Fig. 7



Fig. 8

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | | Poles/Throws | AMPS 125VAC | AMPS 250VAC | Actuator Color | Actuator Material | Imprinting Color and Marking | Mounting Hole | Spec. Drawing Page No. |
|-----------------|---------------|------------|------------------|-----|--------------|-------------|-------------|----------------|-------------------|------------------------------|-----------------|------------------------|
| 35-3760 | 35-3760-BU | 1 | (On) | Off | SPST | 15* | 10 | White | Nylon | | 0.550" x 1.125" | I-19 A |
| 35-691 | 35-691-BU | 2 | On | Off | SPST | 16 | 10 | Black | Nylon | | 0.550" x 1.125" | I-19 B |
| 35-693 | 35-693-BU | 3 | On | Off | SPST | 16 | 10 | Black | Nylon | Red On/Off | 0.550" x 1.125" | I-19 B |
| 35-694 | 35-694-BU | 2 | On | Off | SPDT | 16 | 10 | Black | Nylon | | 0.550" x 1.125" | I-19 B |
| 35-3030 | 35-3030-BU | 3 | On | Off | SPST | 16* | 10 | Black | Nylon | Red On/Off | 0.550" x 1.125" | I-19 B |

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | | Poles/Throws | AMPS 125VAC | AMPS 250VAC | HP 125/250VAC | Actuator Material | Imprinting Color and Marking | Mounting Hole | Spec. Drawing Page No. |
|-----------------|---------------|------------|------------------|-----|--------------|-------------|-------------|---------------|-------------------|------------------------------|-----------------|------------------------|
| 35-3600 | 35-3600-BU | 4 | On | Off | SPST | 15 | 10 | 3/4 | Black Nylon | | 0.830" x 1.450" | I-19 D |
| 35-3610 | 35-3610-BU | 4 | On | On | SPDT | 15 | 10 | 3/4 | Black Nylon | | 0.830" x 1.450" | I-19 D |
| 35-3620 | 35-3620-BU | 4 | On | Off | SPDT | 15 | 10 | 3/4 | Black Nylon | | 0.830" x 1.450" | I-19 D |
| 35-3630 | 35-3630-BU | 4 | On | Off | DPST | 15 | 10 | 3/4 | Black Nylon | | 0.830" x 1.450" | I-19 D |
| 35-3636 | 35-3636-BU | 4 | On | Off | SPST | 20 | † | 1-1/2 | Black Nylon | | 0.830" x 1.450" | I-19 D |
| 35-3640 | 35-3640-BU | 4 | On | On | DPDT | 15 | 10 | 3/4 | Black Nylon | | 0.830" x 1.450" | I-19 D |
| 35-3650 | 35-3650-BU | 4 | On | Off | DPDT | 15 | 10 | 3/4 | Black Nylon | | 0.830" x 1.450" | I-19 D |
| 35-3660 | 35-3660-BU | 4 | (On) | Off | DPST | 15 | 10 | 3/4 | Black Nylon | | 0.830" x 1.450" | I-19 D |
| 35-3670 | 35-3670-BU | 4 | (Off) | On | DPST | 15 | 10 | 3/4 | Black Nylon | | 0.830" x 1.450" | I-19 D |
| 35-3680 | 35-3680-BU | 4 | (On) | On | DPDT | 15 | 10 | 3/4 | Black Nylon | | 0.830" x 1.450" | I-19 D |
| 35-3690 | 35-3690-BU | 4 | (On) | Off | DPDT | 15 | 10 | 3/4 | Black Nylon | | 0.830" x 1.450" | I-19 D |
| 35-3695 | 35-3695-BU | 4 | (On) | Off | DPDT | 15 | 10 | 3/4 | Black Nylon | | 0.830" x 1.450" | I-19 D |
| 35-3710 | 35-3710-BU | 4 | On | Off | SPST | 16 | 10 | 3/4 | Black Nylon | | 0.550" x 1.125" | I-19 C |
| 35-3720 | 35-3720-BU | 4 | On | On | SPDT | 16 | 10 | 3/4 | Black Nylon | | 0.550" x 1.125" | I-19 C |

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | | Poles/Throws | AMPS 125VAC | AMPS 250VAC | HP 250 VAC | Actuator Material | Imprinting Color and Marking | Mounting Hole | Spec. Drawing Page No. |
|-----------------|---------------|------------|------------------|-----|--------------|-------------|-------------|------------|-------------------|------------------------------|-----------------|------------------------|
| 35-620 | 35-620-BU | 5 | On | Off | DPST | 15 | 10 | 1/4 | Red Poly | White On/Off | 0.866" x 1.102" | I-19 E |
| 35-640 | 35-640-BU | 6 | On | On | SPDT | 16 | 16 | 1 | Black Nylon | | 1.100" x 0.453" | I-19 F |
| 35-695 | 35-695-BU | 7 | (On) | Off | (On) | 16 | 16 | 1 | Black Plastic | | 0.550" x 1.180" | I-19 F |
| 35-654 | 35-654-BU | 8 | On | Off | DPST | 20 | 15 | N/R | Black Plastic | | 1.000" x 1.125" | I-19 G |

Notes: (On) = Momentary On N/R = Not Rated † = 20A @ 277VAC and 2 H.P. @ 250VAC
 *3/4 H.P. @ 125/250VAC All of the Above have Quick Connect .250" Terminals

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.

All quantities are single; BU's are packages of 25 Unless otherwise noted.

STANDARD APPLIANCE ROCKERS (Cont.)

