


Raychem E-150 LOW-PROFILE END SEAL KIT





PRODUCT OVERVIEW

The E-150 is a cold-applied low-profile end seal. It is designed for use with the following Raychem brand heating cables: BTV, QTVR, XTV, and KTV. Use the E-150 in applications with temperatures ranging from -60°F to 420°F (-50°C to 215°C). It is approved by FM, CSA, and PTB for use in hazardous locations.

The unique design of the E-150 suits the demanding requirements of the industrial environment. The low-profile housing can be installed on pipes and other surfaces. A spring-loaded grommet makes a first seal to maintain a watertight connection, while the silicone-free, noncuring sealant used in the Raychem sealing boot adds a second seal, providing additional protection.

The rugged construction makes the E-150 resistant to impact and suitable for high-temperature and chemical exposure.

The end seal requires no heat source for installation and it is re-enterable, making maintenance fast and easy. Each kit contains all the necessary materials to do one end termination.

DESCRIPTION

Cold-applied end seal for use with BTV, QTVR, XTV, and KTV heating cables

KIT CONTENTS

- 1 end seal enclosure housing
- 1 sealing grommet assembly
- 1 sealing boot
- 1 identification label

APPROVALS

Hazardous Locations







CLI, ZN2, AEx e II T⁽¹⁾



ll 2G Ex e ll ll 2D Ex tD A21 IP66 PTB 09 ATEX 1068U



09-IFx-0004X Ex e IIC T* Gb




IECEx PTB 09.0043U IECEX Ex e ll Ex tD A21 IP66



Ex e II T^[1]

 $^{(1)}$ For T-rating, see heating cable or design documentation

DIMENSIONS



PRODUCT SPECIFICATIONS

BTV-CR, BTV-CT, QTVR-CT, XTV-CT, KTV-CT Heating cable capability

Ingress protection NEMA 4X (IP66) -40°F (-40°C) Minimum installation temperature Minimum usage temperature -60°F (-50°C) Maximum pipe temperature 420°F (215°C)

Operating voltage 277 Vac for FM, CSA; 254 Vac for PTB

MATERIALS OF CONSTRUCTION

Enclosure, end plate, and shim Engineered polymer, black

Silicone rubber Sealing grommet and core sealer Stainless steel Screws, compression spring,

reinforcement plate

ORDERING DETAILS

Catalog number E-150 979099-000 Part number Weight 0.6 lb (0.3 kg)



WWW.PENTAIRTHERMAL.COM

NORTH AMERICA

Tel: +1.800.545.6258 Fax: +1.800.527.5703 Tel: +1.650.216.1526 Fax: +1.650.474.7711 thermal.info@pentair.com **EUROPE, MIDDLE EAST, AFRICA**

Tel: +32.16.213.511 Fax: +32.16.213.603 thermal.info@pentair.com ASIA PACIFIC

Tel: +86.21.2412.1688 Fax: +86.21.5426.2917 cn.thermal.info@pentair.com **LATIN AMERICA**

Tel: +1.713.868.4800 Fax: +1.713.868.2333 thermal.info@pentair.com

Pentair, BTV, QTVR, XTV, and KTV are owned by Pentair or its global affiliates. All other trademarks are the property of their respective owners. Pentair reserves the right to change specifications without prior notice.

© 2001-2013 Pentair.