


# MILWAUKEE® TOOL SDS PLUS ROTARY HAMMERS LINE-UP

**Milwaukee** Nothing but HEAVY DUTY.®

**RED LITHIUM™**

## INDUSTRY'S ONLY UNIVERSAL DUST EXTRACTOR



	2412-22XC	5263-21	
			
Capacity	1/2"	5/8"	
Amps / Volts	12V	5.5 Amps	
RPM	0 – 800	0 – 3,700	
BPM	0 – 5,350	0 – 4,400	
Modes	2 modes: Rotary Hammer & Rotation Only	2 modes: Rotary Hammer & Rotation Only	
Antivibration System AVS™	No	Yes	
Weight	3.9 lbs	4.6 lbs	

	2605-22	5262-21	
			
Capacity	7/8"	7/8"	
Amps / Volts	18V	7.0 Amps	
Impact Energy	1.8 ft-lb (2.4 J)	1.8 ft-lb (1.8 J)	
RPM	0 – 1,400	0 – 1,500	
BPM	0 – 4,800	0 – 5,625	
Modes	3 modes: Rotary Hammer, Hammer Only & Rotation Only	3 modes: Rotary Hammer, Hammer Only & Rotation Only	
Antivibration System AVS™	Yes	No	
Weight	7.2 lbs	5.8 lbs	

	0756-22	5363-21	5359-21
			
Capacity	1"	1"	1-1/8"
Amps / Volts	28V	7.0 Amps	7.4 Amps
Impact Energy	2.1 ft-lb (2.8 J)	2.0 ft-lb (2.0 J)	2.5 ft-lb (3.4 J)
RPM	0 – 1,400	0 – 1,400	0 – 980
BPM	0 – 4,700	0 – 5,980	0 – 4,200
Modes	3 modes: Rotary Hammer, Hammer Only & Rotation Only	3 modes: Rotary Hammer, Hammer Only & Rotation Only	3 modes: Rotary Hammer, Hammer Only & Rotation Only
Antivibration System AVS™	Yes	Yes	Yes
Weight	9.6 lbs	8.0 lbs	8.3 lbs



2306-22

**NEW**  
**M12 HAMMERVAC™**  
**UNIVERSAL**  
**DUST EXTRACTOR**

Scan to See More





## M12 HAMMERVAC™ UNIVERSAL DUST EXTRACTOR

Compatible with major power tool brands of SDS Plus Rotary Hammers and AC/DC Hammer Drills, the M12™ HAMMERVAC™ Universal Dust Extractor is the industry's only UNIVERSAL dust extractor. Featuring a replaceable, certified HEPA filter for high quality debris filtration, the user is able to replace the filter independently of the dust box to cost-effectively maintain suction efficiency. Powered by the M12™ REDLITHIUM™ battery pack for maximum portability, the M12™ HAMMERVAC™ Universal Dust Extractor is compatible with the entire M12™ System, now offering over 50 cordless Lithium-Ion products.



### UNIVERSAL HANDLE SYSTEM

Utilizes three adjustable side handle collars to fit major brands of SDS Plus Rotary Hammers and AC/DC Hammer Drills.



**REPLACEABLE, CERTIFIED HEPA FILTER**



**99.97% EFFICIENT AT REMOVING PARTICLES 0.3µm & ABOVE**

### ADDITIONAL FEATURES

- Self-Powered by M12™ REDLITHIUM™ Battery Pack: No cords or hoses for maximum portability
- 3-Mode Switch with Auto-On: Auto-On mode turns HAMMERVAC™ on and off automatically
- Lightweight: Only 3.3 lbs. to minimize fatigue in overhead and horizontal drilling

### HAMMERVAC™ ACCESSORIES



3 HEPA Filter Replacement  
49-90-2306



Dust Box, HEPA Filter and Lid  
49-90-2340



2 Pc Nozzle Replacement  
49-90-2300



Crevice Tool  
49-90-2325