BIG HAWG™ HOLE CUTTERS

FAST CUTTING

■ Aggressive tooth geometry for up to 10X faster cutting than hole saws

LONG LIFE

■ Cuts up to 600 holes in wood without needing to be resharpened

Size	Part Number	With Pilot Bit
1-3/8"	49-56-8995	49-56-9110
2-1/8"	49-56-9000	49-56-9120
2-1/4"	49-56-9005	-
2-9/16"	49-56-9010	49-56-9130
3"	49-56-9020	-
3-3/8"	49-56-9025	-

DURABLE

■ Three hardened steel teeth provide maximum durability against unintended nail impacts

EASY PLUG REMOVAL

■ Wide and deep gullets for easy plug removal

Size	Part Number	With Pilot Bit
3-5/8"	49-56-9030	-
4-1/4"	49-56-9045	-
4-5/16"	49-56-9047	-
4-5/8"	49-56-9050	-
5-1/4"	49-56-9055	-
6-1/4"	49-56-9065	-

BIG HAWG™ HOLE CUTTER KITS







8 Pc Plumbers BIG HAWG" Hole Cutter Kit 49-56-9080

Includes:

- (1) Each BIG HAWG[™] hole cutters (2-1/8", 2-9/16", 3-5/8")
- (1) Arbor with pilot bit
- (2) Additional pilot bits
- (1) Diamond file
- (1) Hex wrench

Includes:

- (1) Each BIG HAWG[™] hole cutters (2-1/8", 2-9/16", 3-5/8", 4-5/8")
- (1) Arbor with pilot bit
- (2) Additional pilot bits
- (1) Diamond file
- (1) Hex wrench

Includes:

- (1) Each BIG HAWG[™] hole cutters (2-1/8", 2-1/4", 2-9/16", 3", 3-5/8", 4-1/4")
- (1) Arbor with pilot bit
- (2) Additional pilot bits
- (1) Diamond file
- (1) Hex wrench

BIGHAWG[™]



HOLE SAWS

UP TO HOLES WITHOUT

BIG HAWG™ HOLE CUTTER **ACCESSORIES**

Description	Part Number
BIG HAWG™ File	48-09-5055
BIG HAWG™ Pilot Bit	48-27-1401
BIG HAWG™ Hole Cutter Arbor	49-56-9105

SHIP AUGERS

DURABLE

■ Hardened tip for added nail durability

FAST CHIP REMOVAL

■ Coated flutes for fast chip removal





Size	Part Number	Shank	Overall Length	Twist Length
3/8"	48-13-0373	5/16"	6"	3"
1/2"	48-13-0503	5/16"	6"	3"
5/8"	48-13-0623	7/16"	6"	3"
11/16"	48-13-0683	7/16"	6"	3"
3/4"	48-13-0753	7/16"	6"	3"
13/16"	48-13-0813	7/16"	6"	3"
7/8"	48-13-0873	7/16"	6"	3"
15/16"	48-13-0933	7/16"	6"	3"
1"	48-13-1003	7/16"	6"	3"
1-1/16"	48-13-1063	7/16"	6"	3"
1-1/8"	48-13-1123	7/16"	6"	3"
1-1/4"	48-13-1253	7/16"	6"	3"
1-3/8"	48-13-1373	7/16"	6"	3"
1-1/2"	48-13-1503	7/16"	6"	3"

Size	Part Number	Shank	Length	Length
3/8"	48-13-5500	5/16"	18"	15"
7/16"	48-13-5520	5/16"	18"	15"
1/2"	48-13-5540	5/16"	18"	15"
9/16"	48-13-5560	7/16"	18"	15"
5/8"	48-13-5620	7/16"	18"	15"
11/16"	48-13-5680	7/16"	18"	15"
3/4"	48-13-5750	7/16"	18"	15"
13/16"	48-13-5810	7/16"	18"	15"
7/8"	48-13-5870	7/16"	18"	15"
15/16"	48-13-5930	7/16"	18"	15"
1"	48-13-6000	7/16"	18"	15"
1-1/16"	48-13-6010	7/16"	18"	15"
1-1/8"	48-13-6120	7/16"	18"	15"
1-1/4"	48-13-6250	7/16"	18"	15"
1-3/8"	48-13-6370	7/16"	18"	15"
1-1/2"	48-13-6500	7/16"	18"	15"

SHIP AUGER SET

3 Pc Ship Auger Bit Set (18") 49-13-3000



1/2", 3/4", 1"

