



Nothing but **HEAVY DUTY**®

## CARBIDE TOOTH CUTTERS FOR SHEET METAL

### CLEAN HOLES

- Drills burr-free holes
- Specifically designed for hand held applications to produce drill press quality holes

### LONG LIFE

- Carbide tips stay sharper longer than high-speed steel or bi-metal cutters

### VERSATILE

- For material up to 3/16" thick
- Ideal for stainless steel, structural steel studs and electrical boxes



Size	Metric	Part Number
3/4"	19 mm	49-57-8305
7/8"	22 mm	49-57-8309
1"	25 mm	49-57-8311
1-1/8"	29 mm	49-57-8315
1-7/32"	31 mm	49-57-8317
1-1/4"	32 mm	49-57-8319
1-5/16"	33 mm	49-57-8321
1-3/8"	35 mm	49-57-8323
1-7/16"	37 mm	49-57-8325
1-1/2"	38 mm	49-57-8327
1-3/4"	44 mm	49-57-8329
2"	51 mm	49-57-8331
2-1/8"	54 mm	49-57-8333
2-1/4"	57 mm	49-57-8335
2-3/8"	60 mm	49-57-8337
2-1/2"	64 mm	49-57-8339
2-5/8"	67 mm	49-57-8341
3"	76 mm	49-57-8343

## SHEET METAL CARBIDE TOOTH CUTTER KITS



5 Pc Electrician's Kit 49-22-8300	7 Pc Electrician's Kit 49-22-8310
<b>Includes:</b> <ul style="list-style-type: none"> <li>7/8", 1-1/8", 1-3/8" carbide steel plate cutters</li> <li>Arbor with pilot bit and one additional pilot bit</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>7/8", 1-1/8", 1-3/8", 1-3/4" &amp; 2" carbide sheet metal cutters</li> <li>Arbor with pilot bit and one additional pilot bit</li> </ul>

## CARBIDE TOOTH CUTTERS FOR STEEL PLATE

### CLEAN HOLES

- Drills burr-free holes

### LONG LIFE

- Carbide tips stay sharper longer than high-speed steel or bi-metal cutters

### VERSATILE

- For material up to 1/2" thick
- Ideal for stainless steel, structural steel studs and electrical boxes



Size	Metric	Part Number
11/16"	18 mm	49-57-8201
3/4"	19 mm	49-57-8203
13/16"	21 mm	49-57-8205
7/8"	22 mm	49-57-8207
15/16"	24 mm	49-57-8209
1"	25 mm	49-57-8211
1-1/16"	27 mm	49-57-8213
1-1/8"	29 mm	49-57-8215
1-3/16"	30 mm	49-57-8217
1-1/4"	32 mm	49-57-8219
1-5/16"	33 mm	49-57-8221
1-3/8"	35 mm	49-57-8223
1-7/16"	37 mm	49-57-8225
1-1/2"	38 mm	49-57-8227

## STEEL PLATE CARBIDE TOOTH CUTTER KITS



5 Pc Contractor's Kit 49-22-8200	7 Pc Contractor's Kit 49-22-8210
<b>Includes:</b> <ul style="list-style-type: none"> <li>11/16", 13/16" &amp; 15/16" carbide steel plate cutters</li> <li>Arbor with pilot bit and one additional pilot bit</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>11/16", 13/16", 15/16", 1-1/8" &amp; 1-3/8" carbide steel plate cutters</li> <li>Arbor with pilot bit and one additional pilot bit</li> </ul>

## ARBORS AND PILOT BITS FOR CARBIDE TOOTH CUTTERS

### QUICK CHANGE ARBOR



Description	Part Number
Quick Change Arbor For All Carbide Cutters	49-57-0035
Pilot Bit For 49-57-0035 Quick Change Arbor	49-57-0038
Ejector Spring For 49-57-0035 Quick Change Arbor	40-50-8780

### RETRACTABLE PIN ARBOR



Description	Part Number
Centering Pin Arbor With Detachable Drill Cap*	49-57-0037
Drill Cap For 49-57-0037 Quick Change Arbor*	42-52-1015

\*Drill cap is for drilling a pilot hole if used in a hand held application