


Raychem ACCESSORIES




ATTACHMENT PRODUCTS


Catalog number	Part number	Description
GT-66	C77220-000	66 ft (20 m) roll of glass tape for attaching heating cable to pipe. Not for stainless steel pipes or for installation temperatures below 40°F (5°C).




GS-54	C77221-000	54 ft (16.5 m) roll of glass tape for attaching heating cable to pipe. For stainless steel pipes or for any installation below 40°F (5°C).
-------	------------	--



AT-180	158139-000	180 ft (55 m) roll of aluminum tape for attaching heating cables and thermostat sensors to pipes and tanks. Minimum installation temperature: 32°F (0°C). Dimensions: 2.5 in wide, 5 mils thick.
--------	------------	--



Pipe straps	Part number	Description
PS-01	C77211-000	For conduit ≤ 1 in
PS-03	C77212-000	For connection kits on pipes with dimensions ≤ 2 in
PS-10	C77213-000	For connection kits on pipes with dimensions 2 in – 10 in
PS-20	C77216-000	For connection kits on pipes with dimensions 10 in – 19.5 in Used to secure connection kits and brackets to pipes. Order by pipe diameter, as shown above.




LABELS

Catalog number	Part number	Description
ETL	C77203-000	“Electric Traced” label for identifying traced pipes and tanks.




ACCESSORIES

GLAND ENTRY KIT


Catalog number	Part number	Description	Kit Contents	
			Qty	Description
C75-100-A 	000539-000	A NEMA 4X-rated gland kit used to transition heating cables into a junction box when making connections off of a pipe or tank. It may be used for power, splice, or tee connections. For use with Raychem brand BTV, QTVR, XTV, KTV ⁽¹⁾ , VPL, and LBTV2-CT ⁽²⁾ heating cables. The kit does not include the junction box, flexible tubing, or tape that are required to make a complete connection.	1	Red grommet
			1	Gland with threaded inserts
			1	Gland with screws
			1	Gland gasket
			1	Locknut
			1	Green / yellow tube
			1	CS-100 core sealer
			1	Terminal block
			⁽¹⁾ For KTV only, order PMK-GP-10 grommet (P/N 700823)	
			⁽²⁾ For LBTV2-CT only, order HCS-100-A heat-shrink core sealer (P/N 257649) and PMK-GK-10 grommet (P/N 222724)	

SINGLE-ENTRY TRANSITION KIT

Catalog number	Part number	Description	Kit Contents	
			Qty	Description
JS-100-A 	166639-000	Junction box stand for use with Raychem brand BTV, QTVR, XTV, KTV, and VPL heating cables. A separate customer-supplied NEMA 4X junction box is required.	1	Stand assembly
			1	Lubricant
			1	Adapter for small pipes
			1	Cable tie
			1	Green / yellow tube
			1	CS-100 cold-applied core sealer
			1	JS-100 transition
			1	1-inch locknut

COLD-APPLIED CORE SEALER

Catalog number	Part number	Description
CS-100-A	232949-000	Replacement cold-applied core sealer for Raychem brand BTV, QTVR, XTV, KTV, and VPL heating cables








CONDUIT DRAIN


Catalog number	Part number	Description
JB-DRAIN-PLUG-3/4IN	278621-000	Pentair Thermal Management recommends the use of this 3/4-in conduit drain with each JBS-100 and JBM-100, and other enclosures with associated conduits, to prevent condensate from collecting in the box.



BRACKETS, ADAPTERS

Catalog number	Part number	Description
JBS-SPA	E90515-000	Adapter for mounting E-100, JBS-100, and JS-100 to small pipe (\leq 1 inch nominal diameter).
		
JBM-SPA	D55673-000	Adapter for mounting JBM-100 and T-100 to small pipe (\leq 1 inch nominal diameter).
		
SB-100-T	279613-000	Adapter for mounting E-100, E-100-L, and JBS-100 connection kits on a tank surface.
		
UMB	263757-000	Universal mounting bracket for mounting thermostats and other equipment on a pipe.
		
JB-SB-25	471139-000	Stainless-steel mounting bracket for RAYSTAT-EX-03-A thermostat.
		

HELICAL FLEXIBLE PLASTIC TUBING

Catalog number	Part number	Description
HCTE-1000	3679754004	Helical flexible plastic tubing for C75-100-A and HAK-C-100 connection kits.
		



WWW.PENTAIRTHERMAL.COM

NORTH AMERICA

Tel: +1.800.545.6258
Fax: +1.800.527.5703
Tel: +1.650.216.1526
Fax: +1.650.474.7711
thermal.info@pentair.com

EUROPE, MIDDLE EAST, AFRICA

Tel: +32.16.213.511
Fax: +32.16.213.603
thermal.info@pentair.com

ASIA PACIFIC

Tel: +86.21.2412.1688
Fax: +86.21.5426.2917
cn.thermal.info@pentair.com

LATIN AMERICA

Tel: +1.713.868.4800
Fax: +1.713.868.2333
thermal.info@pentair.com

Pentair, BTV, QTVR, XTV, KTV, VPL, LBT2, JBS, and JBM are owned by Pentair or its global affiliates. All other trademarks are the property of their respective owners. Pentair reserves the right to change specifications without prior notice.

© 2001–2013 Pentair.