

EZL500 Thermal Label Printer



EZL500 Thermal Label Printer

Cat. Number	Description	UPC Number
EZL500	Handheld Thermal Label Printer (includes EZL500 Thermal Label Printer, EZ-1030C-WN label cassette, six AA batteries, quick-start guide and user's manual)	782609-91656
EZL500-KIT	Handheld Thermal Label Printer Kit with Accessories (includes EZL500 Thermal Label Printer, EZ-1030C-MP and EZ-1030C-WN label cassettes, PA-EZL500 power adapter, MS-EZL500 magnet strap, PCS-EZL500 PC software and USB cable, RB-EZL500 rechargeable battery, quick-start guide, user's manual and CC-EZL500 carrying case)	782609-91657



EZL500 Accessories

Cat. Number	Description	UPC Number
PA-EZL500	EZL500 Power Adapter	786209-91682
MS-EZL500	Magnet Strap for EZL500	786209-91683
PCS-EZL500	PC Software and USB Cable for EZL500	786209-91685
CC-EZL500	Hard Carrying Case for EZL500	786209-91686
RB-EZL500	EZL500 Rechargeable Battery	786209-92262

EZL500 Thermal Label Printer Tapes

- **Nylon** — Excellent for wire and cable wrapping on curved, textured and highly textured surfaces, these flexible labels feature EZ-Peel split backs and industrial-strength adhesive
- **Polyester** — Perfect for general labeling on flat or textured surfaces, these labels also come with EZ-Peel split backs and industrial-strength adhesive
- **Heat-Shrink** — Made of flame-retardant polyolefin with 3:1 shrink ratio for extra protection and insulation of wire and cable, these labels meet MIL-DTL-23053/5 classes 1 and 3 standards
- **Vinyl** — Able to resist oil, dirt, grime and solvents on smooth, textured or curved surfaces, this flexible label features an EZ-Peel split back and industrial-strength adhesive; it's excellent for indoor/outdoor use



EZ-1230C-WN



EZ-3430C-WP

EZL500 Label Printer Tapes

Cat. Number	Material	Color	Width	UPC Number
EZ-3830C-WN	Nylon	White	3/8"	786209-91658
EZ-1230C-WN	Nylon	White	1/2"	786209-91659
EZ-3430C-WN	Nylon	White	3/4"	786209-91660
EZ-1030C-WN	Nylon	White	1"	786209-91661
EZ-3830C-YN	Nylon	Yellow	3/8"	786209-91662
EZ-1230C-YN	Nylon	Yellow	1/2"	786209-91663
EZ-3430C-YN	Nylon	Yellow	3/4"	786209-91664
EZ-1030C-YN	Nylon	Yellow	1"	786209-91665
EZ-3830C-WP	Polyester	White	3/8"	786209-91666
EZ-1230C-WP	Polyester	White	1/2"	786209-91667
EZ-3430C-WP	Polyester	White	3/4"	786209-91668
EZ-1030C-WP	Polyester	White	1"	786209-91670
EZ-3830C-MP	Polyester	Metallic	3/8"	786209-91671
EZ-1230C-MP	Polyester	Metallic	1/2"	786209-91672
EZ-3430C-MP	Polyester	Metallic	3/4"	786209-91673
EZ-1030C-MP	Polyester	Metallic	1"	786209-91674
EZ-1412C-WHS	Heat-Shrink	White	1/4"	786209-91675
EZ-3812C-WHS	Heat-Shrink	White	3/8"	786209-91676
EZ-1212C-WHS	Heat-Shrink	White	1/2"	786209-91677
EZ-1412C-YHS	Heat-Shrink	Yellow	1/4"	786209-91678
EZ-3812C-YHS	Heat-Shrink	Yellow	3/8"	786209-91679
EZ-1212C-YHS	Heat-Shrink	Yellow	1/2"	786209-91680
EZ-1030C-SL	Self-Laminating Vinyl	White/Clear	1"	786209-91681

www.tnb.com

Thomas & Betts

Please ask your Thomas & Betts sales representative for a complete catalog of quality Thomas & Betts electrical products or visit us at www.tnb.com. For customer service, call 1-800-816-7809. For technical questions, call 1-888-862-3289.

Thomas & Betts Corporation
Electrical Division
8155 T&B Boulevard
Memphis, TN 38125
901-252-5000

Thomas & Betts Ltd.
700 Thomas Avenue
Iberville, Québec J2X 2M9
450-347-5318