



8" Cable Ties  
HPWCVFxx8



Bulk Spool  
HVFBK5600



Basic Fasteners  
MCCMV9xx10



Screw Mount  
MCCMV9OS10  
MCCMV9BS10

**VELCRO® Brand ONE-WRAP® Cable Ties**

Unit of measure: one 10-pack of straps

Length Inches (mm)	Max. Bundle Diameter Inches (mm)	Color	Catalog No.
8" (203)	2.5" (64)	Black	<b>HPWCVFBK8</b>
		Blue	<b>HPWCVFBL8</b>
		Orange	<b>HPWCVFOR8</b>
		Red	<b>HPWCVFRD8</b>
		Yellow	<b>HPWCVFYL8</b>

**Bulk VELCRO® Spool**

Width Inches (mm)	Length Feet (mm)	Unit of Measure	Catalog No.
1" (25)	10' (3048)	Cut to length	<b>HPWCVFBK120</b>
0.625" (16)	75' (22,860)	Cut to length	<b>HVFBK5875</b>
0.5" (13)	75' (22,860)	Cut to length	<b>HVFBK575</b>
0.5" (13)	75' (22,860)	Rip to length	<b>HVFBK575S</b>
0.5" (13)	600' (182,880)	Cut to length	<b>HVFBK5600</b>

**Basic VELCRO® Brand Fasteners**

Unit of measure: one 10-pack of straps

Length Inches (mm)	Max. Bundle Diameter Inches (mm)	Color	Catalog No.
22" (559)	7.5" (191)	Black	<b>MCCMV22BK10</b>
		Black	<b>MCCMV9BK10</b>
		Blue	<b>MCCMV9BL10</b>
		Orange	<b>MCCMV9OR10</b>
		Pink	<b>MCCMV9PK10</b>
		Red	<b>MCCMV9RD10</b>
		Yellow	<b>MCCMV9YL10</b>
		5" (127)	1.4" (36)
Blue	<b>MCCMV5BL10</b>		
Orange	<b>MCCMV5OR10</b>		
Pink	<b>MCCMV5PK10</b>		
Red	<b>MCCMV5RD10</b>		
Yellow	<b>MCCMV5YL10</b>		

**Screw-Mount, Reusable Cable Ties**

Unit of measure: one 10-pack of straps

Length Inches (mm)	Max. Bundle Diameter Inches (mm)	Color	Catalog No.
9" (229)	2.5" (64)	Black	<b>MCCMV9BS10</b>
		Orange	<b>MCCMV9OS10</b>

VELCRO® and ONE-WRAP® are registered trademarks of Velcro Industries B.V.