

AUDIO | VIDEO CONNECTIVITY

TracJack Solutions

OR-637000, OR-42100002 TracJack Solutions



TracJack Solutions

TracJack® footprint is front loading and supports a number of A/V and data modules. It's ideal for combining A/V with our high performance Clarity® workstation products. The TracJack footprint can also be used with Series II® through the use of an adapter bezel.

| PART NO. | DESCRIPTION |
|--------------|--|
| OR-63700058* | RCA red female-to-female |
| OR-63700085 | RCA blue, female-to-female |
| OR-63700059* | RCA white female-to-female |
| OR-63700060* | RCA yellow female-to-female |
| OR-63700071 | RCA red to 110 |
| OR-63700084 | RCA blue to 110 |
| OR-63700070 | RCA white to 110 |
| OR-63700047 | RCA yellow to 110 |
| OR-63700046 | Pair of RCA to 110 (1) red, (1) black, 180° exit |
| OR-63700025 | S-Video to 110 |
| OR-63700069 | 3.5mm stereo jack |
| OR-63700023 | BNC 75 ohm, female-to-female |
| OR-63700006 | F Conn 75 ohm, female-to-female |
| OR-63700087 | F Conn 75 ohm, recessed, female-to-female |
| OR-42100002 | TracJack blank, 10pk |

Notes: Standard color for TracJack modules is fog white. Also available in -99 Wiremold® ivory and -88 white. Contact Legrand sales department for other colors.
*Only available in fog white.

AUDIO | VIDEO CONNECTIVITY

TechChoice Keystone Solutions

OR-KS**TechChoice Keystone Solutions**

OR-KSHDMI



OR-KSSV



OR-KSSVIDC



OR-KSRCAR



OR-KSRCAG



OR-KSRCABL



OR-KSRCAY



OR-KSRCAW



OR-KSRCAB



OR-KS35ST



OR-KS35STST



OR-KS14ST



OR-KSUBAA



OR-KSUBAB



OR-KSBP



OR-KSBNC75



OR-KSBNC



OR-KSFCN



OR-KSFCNR-13



OR-KSB10

TechChoice Keystone Solutions

TechChoice® Keystone footprint is a rear loading style module that comes in a variety of A/V connector types as well as Category 5e and 6 data connectivity. It's ideal for creating a quality solution for A/V and data connectivity. The Keystone footprint can also be used with Series II® through the use of an adapter bezel (OR-40300656).

| PART NO. | DESCRIPTION |
|-------------|---|
| OR-KSHDMI | HDMI, female-to-female, 19-pin |
| OR-KSSV | S-Video to 110 |
| OR-KSSVIDC | S-Video, female-to-female |
| OR-KSRCAR | RCA red to 110 |
| OR-KSRCAG | RCA green to 110 |
| OR-KSRCABL | RCA blue to 110 |
| OR-KSRCAY | RCA yellow to 110 |
| OR-KSRCAW | RCA white to 110 |
| OR-KSRCAB | RCA black to 110 |
| OR-KS35ST | 3.5mm, stereo jack, female-to-female |
| OR-KS35STST | 3.5mm, stereo jack, female-to-screw term |
| OR-KS14ST | 1/4" stereo jack, female-to-solder |
| OR-KSUBAA | USB 2.0 A-A, female-to-female |
| OR-KSUBAB | USB 2.0 A-B, female-to-female |
| OR-KSBP | Binding post, set of (2) |
| OR-KSBNC75 | BNC 75 ohm, female-to-female, 75 ohm |
| OR-KSBNC | BNC 50 ohm, female-to-female, 50 ohm |
| OR-KSFCN | F Conn 75 ohm, female-to-female |
| OR-KSFCNR | F Conn 75 ohm, recessed, female-to-female |
| OR-KSB10 | Blank, 10pk |