


Sta-Kon® Installation Kits



ORG-2



Wiring Organizer

Cat. No.	Description	Std. Pkg.	Wt.
ORG2	Heavy Duty Steel Drawer with (17) compartments to hold Sta-Kon® terminals, Color-Keyed® lugs, Ty-Rap® cable ties, and other small parts	1	4

Drawer does not include Thomas & Betts products.

Sta-Kon® Terminal Kit

For residential or light commercial installations we recommend this proven assortment of popular Sta-Kon® vinyl terminals. This kit includes a WT112M crimping tool.

Cat. No.	Description	Std. Pkg.	Wt.
SK-CLASSIQUE	36 2RA18X Butt splices for 22-16 AWG,	1	6.5
	36 18RA-8F Fork terminals for 22-16 AWG,		
	36 18RA-10F Fork terminals for 22-13 AWG,		
	36 18RA-8 Ring terminals for 22-16 AWG,		
	36 18RA-10 Ring terminals for 22-16 AWG,		
	36 RBB217-200 Butt splices for 16-14 AWG,		
	36 14RB-10F Fork terminals for 18-14 AWG,		
	36 18RA-250F Disconnects for 22-18 AWG,		
	36 14RB-8F Fork terminals for 18-14 AWG,		
	36 14RB-8 Ring terminals for 18-14 AWG,		
	36 14RB-10 Ring terminals for 18-14 AWG,		
	25 RCC217-250 Butt splices for 12-10 AWG,		
	25 10RC-8F Fork terminals for 12-10 AWG,		
	25 10RC-10 Ring terminals for 12-10 AWG,		
	20 RC6 Wire joints,		
	1 WT112M Crimping tool		
	50 822D Wire connectors XTP blue #22-#8		

Sta-Kit*

For residential or light commercial installations we recommend this proven assortment of popular Sta-Kon® vinyl terminals. This kit includes a WT112M crimping tool.

Cat. No.	Description	Std. Pkg.	Wt.
STAKIT*	100 2RA18X butt splices for 22-18 AWG,	1	1
	100 2RB14X butt splices for 18-14 AWG,		
	50 2RC10X butt splices for 12-10 AWG,		
	50 10RC-10 ring terminals for 12-10 AWG,		
	50 10RC-10FL locking fork terminals for 12-10 AWG,		
	50 10RC-250F disconnects for 12-10 AWG,		
	100 14RB-10 ring terminals for 18-14 AWG,		
	100 14RB-8FL locking fork terminals for 18-14 AWG,		
	100 14RB-250F disconnects for 18-14 AWG,		
	100 18RA-8F Fork Terminals for 22-18 AWG,		
	100 18RA-6FL locking fork terminals for 22-18 AWG,		
	100 18RA-250F disconnects for 22-18 AWG		
	1 WCMB-0-9		
	1 WT112M crimping tool and 100 TY525M Ty-Rap® cable ties (approx. length 7-1/2)		

* (All splices, terminals and disconnects are vinyl insulated).